



# Southwire™

## DUSK TO DAWN LED BARN LIGHTS

### 35W DUSK TO DAWN LED BARN LIGHT

- Intergrated Photocell Sensor
- Bronze Aluminum housing
- Frosted Polycarbonate Lens
- Suitable for Wet Locations
- 3675 Lumens | 35 Watts
- 5000K Color Temperature
- 120-277Vac 50/60Hz



### 42W DUSK TO DAWN LED BARN LIGHT

- Intergrated Photocell Sensor
- Bronze Aluminum housing
- Frosted Polycarbonate Lens
- Suitable for Wet Locations
- 5000 Lumens | 42 Watts
- 5000K Color Temperature
- 120-277Vac 50/60Hz



### 58W DUSK TO DAWN LED BARN LIGHT

- Intergrated Photocell Sensor
- Bronze Aluminum housing
- Frosted Polycarbonate Lens
- Suitable for Wet Locations
- 7000 Lumens | 58 Watts
- 5000K Color Temperature
- 120-277Vac 50/60Hz



MODEL #	UPC	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
L17BL1036	032886745492	35W Dusk to Dawn LED Barn Light	5.5"	6.5"	10.3"	1.8 lbs.
L17BL2050	03288674550	42W Dusk to Dawn LED Barn Light	5.2"	10"	13.8"	3.4 lbs.
L17BL2065	032886746512	58W Dusk to Dawn LED Barn Light	5.5"	10"	13.8"	3.4 lbs.

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2020 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.