



Southwire™

TOOLS & EQUIPMENT

SIMpull™ FLEXIBLE METAL LEADER FISH TAPE



FTSP45-75FML

FTSP45-125FML

FTSP3-100FML

FTSP3-240FML

FTSP45-240FMLT



Does not break when folded



Weighs less than steel



Does not rust



Faster install time



Swiveling leader

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



SIMpull™ FLEXIBLE METAL LEADER FISH TAPE

- Spiral extruded polymer design reduces the amount of effort required to push or pull the fish tape through EMT or PVC conduit*
- Swiveling flexible metal leader easily glides through bends
- Allows the fish tape to glide through conduit without binding at joints, couplings or 90 degree bends
- Combines the strength of a steel fish tape with greater flexibility than fiberglass fish tapes*



FTSP45-240FMLT



SPECIFICATION

Model #	Stock #	Description	Length (ft.)	Tensile Strength (lbs.)
FTSP45-75NCT	63029801	SIMpull™ Fish Tape 4.5mm 75' Non-Conductive Tip, Large Case	75	380
FTSP3-100NCT	59897201	SIMpull™ Fish Tape 3mm 100' Non-Conductive Tip, Large Case	100	220
FTSP45-125NCT	63163701	SIMpull™ Fish Tape 4.5mm 125' Non-Conductive Tip, Large Case	125	380
FTSP45-240FMLT	63164701	SIMpull™ Fish Tape 4.5mm 240' Flexible Leader & Non-Conductive Tip, Tube	240	380

*When compared to Southwire™ Steel and Fiberglass fish tapes

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.