



Burglar Alarm cable Solid and Stranded CM/CL2 Rated



96222 96238



51101 51112

APPLICATIONS Burglar alarm interconnect cables to controls systems, Class 2 Power Limited Circuit Cable and Communications Cable for General Purpose Applications

CONSTRUCTION

A.) CONDUCTOR 22 AWG solid or stranded Bare Copper
 B.) INSULATION Foam Polypropylene
 C.) COLOR CODE See table
 D.) SHIELDING Unshielded
 E.) ASSEMBLY This cable consists of insulated conductors with an overall extruded jacket.
 F.) JACKET Smooth, round, flexible PVC. Colors: White, Gray, Brown, Beige (Other colors available for minimum order)

COMPLIANCE

A.) FLAME TEST UL 1685 (by UL) / CSA FT1
 B.) CABLE TYPE UL Standard 13 and 444, NEC Articles 725 and 800, CM/CL2
 C.) VOLTAGE 300 V RMS Max.
 D.) TEMPERATURE -20°C to 75°C
 E.) SUITABLE USE: General purpose low voltage and power-limited systems. Suitable for use in indoor use, circuits to NEC Article 725 and 800

FEATURES & OPTIONS: Available in 1000ft or 500 ft packages, reels, or pull-boxes where practicable.



Stock #	DESCRIPTION	AWG	#COND	STRANDS	Rating	NOM. DIA. (Inches)	WEIGHT (Lb/Mft)	COLOR CODE
96222	22/2 Conductors BC	22	2	Solid	CM	0.102	7	Red, Green
96238	22/4 Conductors BC	22	4	Solid	CM	0.117	12	Blk, Red, Yel, Grn
51101	22/2 Conductors BC	22	2	Stranded	CM	0.11	9	Blk, Red
51112	22/4 Conductors BC	22	4	Stranded	CM	0.126	13	Blk, Red, Wht, Grn

