



Southwire™

TOOLS & EQUIPMENT

MINI X-TREME BOX™

The Mini X-Treme Box™ provides more impact and less costly work-site power distribution than our popular full size models. Used along with our restoration adapters, these units are ideal for disaster restoration work where the only available power is from range outlets, dryer outlets or portable generators. Or, they can be used in any situation where a more compact, easier-to-handle unit is desired to safely expand and distribute power on jobsites.

20A PANEL MOUNTED
GFCI ON BOTH ENDS

30A 125/250V
TWIST LOCK FLANGE INLET
(BACK OF UNIT)

20A CIRCUIT BREAKER ON
BOTH ENDS PROTECTS THE
UNIT FROM OVERCURRENT



HEAVY-DUTY HANDLE
INCREASES PORTABILITY

4-20A, 5-20R OUTLETS
(ON BOTH SIDES)

RUBBERIZED FEET KEEP CONNECTIONS
AWAY FROM SURFACE MOISTURE

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



MINI X-TREME BOX™

FEATURES

- OSHA and NEC Compliant, UL Listed, and Certified to CAN/CSA
- Ready to use out of the box
- 8 overload, circuit-breaker protected 20 amp straight blade outlets
- All outlets are GFCI protected with open neutral and over-voltage protection
- Compact size for ease of use
- May be used in vertical or horizontal positions



(18640008)



(19800102)

SPECIFICATIONS

| PART # | 30A POWER INLET | 20A POWER OULETS | OVERLOAD PROTECTION | GFCI PROTECTION | WT (LBS) | STDPK |
|----------|-----------------|------------------|---------------------|----------------------------|----------|-------|
| 19800102 | L14-30 | (8) NEMA 5-20R | (2) 20 A Breakers | (2) 20A GFCI w/ auto reset | 10 | 1 |

POWER DISTRIBUTION EXTENSION CORDS

| PART # | LENGTH | DESCRIPTION | STDK PK | WT (LBS) | MALE END | FEMALE END | POWER FROM |
|----------|--------|--|---------|----------|--------------------|------------|---|
| 18540008 | 10' | 10/4 SE00W Black 14-30P to L14-30R | 4 | 3.99 | 14-30P | L14-30R | Dryer Outlet or 30A Straight Generator Outlet |
| 18640008 | 10' | 10/4 SE00W Black 14-50P to L14-30R | 4 | 4.03 | 14-50P | L14-30R | Range Outlet or 50A Straight Generator Outlet |
| 18450008 | 25' | 10/4 SE00W Black 50A CA-Style to L14-30R | 4 | 9.49 | 50A CA-Style Twist | L14-30R | 50A X-Treme Box |
| 1493 | 25' | 10/4 STW Yellow L14-30P to L14-30R | 2 | 9.05 | L14-30R | L14-30R | 30A Twist-Lock Generator Outlet |

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.