



Southwire™

4" SQUARE COVERS

INDUSTRIAL EXPOSED WORK, RAISED 1/2"

FEATURES

- Crushed corner design allows use of standard box cover screws

APPLICATIONS

- 4" square, 1/2 in raised exposed work covers are used to close a 4" square junction box or to attach a device(s) in a surface mount industrial or commercial setting

STANDARD MATERIAL

- Galvanized steel or 316 stainless steel

CERTIFICATIONS

- UL, cULus Listed



G1929





Southwire™

4" SQUARE COVERS

INDUSTRIAL EXPOSED WORK, RAISED 1/2"



G1930



G1938



G1939



G1935



BP-1935



BPO-1935



G1936



BP-1936



BPO-1936



G1947



G1950



G1941



G1948



G1951



G1932



G1944



G1942



G1943



G1949



G1933



G1937



G1940



G1952



G1929-SS



G1938-SS



G1939-SS



G1935-SS



G1936-SS



G1947-SS



G1950-SS



G1953



C3452



C3543



C3454

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

PART #	DEVICE OPENING(S)	CUBIC INCHES (CM ³)	MASTER QTY.
G1929	BLANK	7.0 (114.8)	50
G1930	1/2" KO CENTERED	7.0 (114.8)	50
G1938	(1) DUPLEX	7.0 (114.8)	50
G1939	(2) DUPLEX	7.0 (114.8)	50
G1935	(1) TOGGLE	7.0 (114.8)	50
BP-1935	(1) TOGGLE, GAS BURNER, RED	7.0 (114.8)	25
BPO-1935	(1) TOGGLE, OIL BURNER, RED	7.0 (114.8)	25
G1936	(2) TOGGLES	7.0 (114.8)	50
BP-1936	(2) TOGGLES, GAS BURNER, RED	7.0 (114.8)	25
BPO-1936	(2) TOGGLES, OIL BURNER, RED	7.0 (114.8)	25
G1947	(1) DECORATOR & GFCI	7.0 (114.8)	50
G1950	(2) DECORATOR/GFCI	7.0 (114.8)	50
G1941	(1) TOGGLE & (1) DUPLEX	7.0 (114.8)	50
G1948	(1) TOGGLE, & (1) DECORATOR/GFCI	7.0 (114.8)	50
G1951	(1) DUPLEX & (1) DECORATOR/GFCI	7.0 (114.8)	50
G1932	(1) 1.406" DIAMETER	7.0 (114.8)	50
G1944	(1) 30-50A 2.141" DIAMETER	7.0 (114.8)	50
G1942	(1) 20A 1.594"DIAMETER	7.0 (114.8)	50
G1943	(1) 30A 1.719" DIAMETER	7.0 (114.8)	50
G1949	(1) 30-60A 2.441" DIAMETER	7.0 (114.8)	50
G1933	(2) 1.406"DIAMETER	7.0 (114.8)	50
G1937	(1) 1.406" DIAMETER & (1) TOGGLE	7.0 (114.8)	50
G1940	(1) 1.406" DIAMETER & (1) DUPLEX	7.0 (114.8)	50
G1952	(1) 1.406" DIAMETER & (1) DECORATOR/GFCI	7.0 (114.8)	50
G1929-SS	BLANK, 316 STAINLESS STEEL	6.5 (106.5)	50
G1938-SS	(1) DUPLEX, 316 STAINLESS STEEL	6.5 (106.5)	50
G1939-SS	(2) DUPLEX, 316 STAINLESS STEEL	6.5 (106.5)	50
G1935-SS	(1) TOGGLE, STAINLESS STEEL	6.5 (106.5)	50
G1936-SS	(2) TOGGLES, 316 STAINLESS STEEL	6.5 (106.5)	50
G1947-SS	(1) DECORATOR & GFCI, 316 STAINLESS STEEL	6.5 (106.5)	50
G1950-SS	(2) DECORATOR/GFCI, 316 STAINLESS STEEL	6.5 (106.5)	50
G1953	(2) 1.60" DIAMETER	7.0(114.8)	50
C3452	(1) TOGGLE & (1) DUPLEX	6.6 (108.5)	50
C3453	(1) 1.406" DIAMETER & (1) DUPLEX	6.6 (108.5)	50
C3454	(1) DUPLEX	6.6 (108.5)	50

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.