



## Mogul LB Conduit Body Wire Capacities

| Part #   | Wire Size | Max #<br>Conductors | Bending Space<br>Requirements |  | Part #   | Wire Size | Max #<br>Conductors | Bending Space<br>Requirements |
|----------|-----------|---------------------|-------------------------------|--|----------|-----------|---------------------|-------------------------------|
| MOLB-350 | 4         | 47                  | 8"                            |  | MOLB-400 | 4         | 60                  | 10"                           |
|          | 3         | 39                  | 8"                            |  |          | 3         | 51                  | 10"                           |
|          | 2         | 33                  | 8"                            |  |          | 2         | 43                  | 10"                           |
|          | 1         | 25                  | 8"                            |  |          | 1         | 32                  | 10"                           |
|          | 0         | 21                  | 8"                            |  |          | 0         | 27                  | 10"                           |
|          | 00        | 17                  | 8"                            |  |          | 00        | 22                  | 10"                           |
|          | 000       | 14                  | 8"                            |  |          | 000       | 18                  | 10"                           |
|          | 0000      | 12                  | 8"                            |  |          | 0000      | 15                  | 10"                           |
|          | 250       | 10                  | 8"                            |  |          | 250       | 12                  | 10"                           |
|          | 300       | 8                   | 8"                            |  |          | 300       | 11                  | 10"                           |
|          | 350       | 7                   | 8"                            |  |          | 350       | 9                   | 10"                           |
|          | 400       | 6                   | 8"                            |  |          | 400       | 8                   | 10"                           |
|          | 500       | 5                   | 8"                            |  |          | 500       | 7                   | 10"                           |
|          | 600       | 4                   | 8"                            |  |          | 600       | 5                   | 10"                           |
|          | 700       | 4                   | 8"                            |  |          | 700       | 5                   | 10"                           |
|          | 750       | 3                   | 8"                            |  |          | 750       | 4                   | 10"                           |
|          | 800       | 3                   | 8"                            |  |          | 800       | 4                   | 10"                           |
|          | 900       | 3                   | 8"                            |  |          | 900       | 4                   | 10"                           |
|          | 1000      | -                   | 8"                            |  |          | 1000      | 3                   | 10"                           |