



Southwire™

SIMPush™ RIGID CONDUIT BODIES

LL TYPE - ALUMINUM

FEATURES

- Gasket NBR Nitrile
- No need to thread conduit
- Works with threaded or non-threaded RMC, IMC, GRC, ARC and rigid stainless steel
- Copper free aluminum, powder coat
- Reusable, tested for up to 100 removal cycles
- Watertight, concrete tight, direct burial rated

APPLICATIONS

- Allows access for inspection, pulling and maintenance

STANDARD MATERIAL

- Copper free aluminum

CERTIFICATIONS

- UL Listed



R-LL-050

| STOCK # | MODEL # | SIZE | QUANTITY PER BAG | OVERALL PRODUCT DIMENSIONS | | | ASSOCIATED REMOVAL TOOL MODEL # | REMOVAL TOOL INCLUDED |
|----------------------------------|-----------|--------|------------------|----------------------------|--------|--------|---------------------------------|-----------------------|
| | | | | HEIGHT | WEIGHT | LENGTH | | |
| RETAIL POLY-BAG PACKAGING | | | | | | | | |
| 65082101 | R-LL-050 | 1/2" | 1 | 5.34" | 2.83" | 1.40" | R-RT-1P | --- |
| 65082201 | R-LL-075 | 3/4" | 1 | 6.11" | 3.09" | 1.64" | R-RT-1P | --- |
| STOCK # | MODEL # | SIZE | QUANTITY PER BOX | HEIGHT | WEIGHT | LENGTH | ASSOCIATED REMOVAL TOOL MODEL # | REMOVAL TOOL INCLUDED |
| CONTRACTOR PACK | | | | | | | | |
| 65082102 | R-LL-050W | 1/2" | 4 | 5.34" | 2.83" | 1.40" | R-RT-1P | --- |
| 65082202 | R-LL-075W | 3/4" | 4 | 6.11" | 3.09" | 1.64" | R-RT-1P | --- |
| 65082302 | R-LL-100W | 1" | 4 | 6.99" | 3.33" | 1.90" | R-RT-2P | --- |
| 65082402 | R-LL-125W | 1-1/4" | 3 | 9.02" | 4.53" | 2.85" | R-RT-2P | --- |
| 65082502 | R-LL-150W | 1-1/2" | 3 | 9.05" | 4.56" | 2.85" | R-RT-3P | --- |

Rev. 0, 06/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.