



# Southwire™

## EMT AND RIGID COMBINATION CONDUIT BODIES WITH COVER AND GASKET

### C TYPE

#### FEATURES

- Combination C type with cover and gasket
- NPT tapered hubs
- Suitable for use in concrete
- NEMA FB 1 rated for wet locations use with threaded rigid metal conduit only

#### APPLICATION

- Provides access to conductors for pulling, splicing and maintenance

#### STANDARD MATERIAL

- Copper free aluminum die cast
- Cover - Stamped steel
- Gasket - Neoprene rubber

#### STANDARD FINISH

- Powder coat

#### CERTIFICATIONS


- UL Standard: 514A
- Fed. Spec. W-C-586D
- NEMA FB 1



C1SSCG



PART #	SIZE	WIRE SIZE MAX. NUMBER	MAX. SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	A	B	C
C1SSCG	1/2"	1	6 AWG	10	100	30	5.35"	1.31"	1.31"
C2SSCG	3/4"	2	6 AWG	10	50	21	6"	1.62"	1.48"
C3SSCG	1"	3	6 AWG	5	25	17	7.06"	1.88"	1.75"
C4SSCG	1-1/4"	3	2 AWG	2	10	12	9.25"	2.50"	2.40"
C5SSCG	1-1/2"	3	2 AWG	2	10	15	9.25"	2.67"	2.40"
C6SSCG	2"	3	2/0 AWG	---	5	10	11.50"	3.29"	3.05"



Rev. 0, 03/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.