



Southwire™

WOBBLELIGHT®

6000 LUMEN SELF-RIGHTING LED JOBSIGHT LIGHT

- Patented Self-Righting Technology
- 360 Light Output
- 5' Power Cord
- Intergrated Carry Handle
- No Hot Surfaces
- 5000K Color Temperature
- 6000 Lumens | 120Vac 50/60Hz | 51 Watts E39 Mogul Base



10000 LUMEN SELF-RIGHTING LED JOBSIGHT LIGHT

- Daisy-Chain Socket
- Patented Self-Righting Technology
- 360 Light Output
- 5' Power Cord
- Intergrated Carry Handle
- Heavy-Duty Steel Dome Design
- 10000 Lumens | 120Vac 50/60Hz | 90 Watts E39 Mogul Base



MODEL #	UPC	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
111208	032886747656	6000 Lumen Self-Righting LED Jobsight Light	25"	15"	15"	16 lbs.
111211	032886747687	10000 Lumen Self-Righting LED Jobsight Light	27"	15"	15"	18 lbs.

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2020 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.