



Southwire™

M550

# Continuity Tester for Data & Coax Cables

THE M550 GIVES INSTANT CONTINUITY STATUS FOR BOTH TWISTED PAIR AND COAXIAL CABLES. FEATURES RUGGED DOUBLE MOLDED TESTER BODY WITH ON-BOARD REMOTE STORAGE AND AN EASY-TO-INTERPRET LED DISPLAY.

● **TEST**  
patch cables or installed cables

● **TESTS**  
shielded, unshielded twisted pair, and coax

● **QUICKLY DETECTS**  
wiring faults in network and coax cables

● **IDENTIFIES**  
correct wiring, opens, shorts, reversals, miswires, split pairs, and shielded cables

● **AUTO POWER-OFF**



Southwire™


TOOLS & EQUIPMENT

[ BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™ ]

1-855-SWT00LS  
(855-798-6657)



Scan code to see more  
Southwiretools.com



## Continuity Tester for Data & Coax Cables



- TEST PATCH CABLES OR INSTALLED CABLES
- IDENTIFIES CORRECT WIRING, OPENS, SHORTS, REVERSALS, MISWIRES, SPLIT PAIRS, AND SHIELDED CABLES
- TESTS SHIELDED, UNSHIELDED TWISTED PAIR, AND COAX
- AUTO POWER OFF



**⚠ WARNING:** Never use on live circuits.

**⚠ ADVERTENCIA:** Nunca to use en circuitos con corriente

Operating Temperature	32°F to 122°F (0°C to 50°C)
Storage Temperature	-4°F to 140°F (-20°C to 60°C)
Humidity	10% to 90% non-condensing
Maximum Voltage between any two pins without damage	60V DC or 55V AC
Batteries	Two "AAA" 1.5V
Cable Types	Shielded or Unshielded: Cat 7, Cat 7a, Cat 6a, Cat 6, Cat 5e, Cat 5, Car 4, Cat 3, Coax
Maximum Coax Cable Length	0 to 1000 ft (305 m)
Minimum Cable Length for Split Pair Detection	1.6 ft (0.5m)
Dimensions	51.1" X 20.5" X 13.0" (13.0 X 5.2 X 3.3 cm)
Weight	4.5 oz (129.4 grams)

### INCLUDES

Data/Video Cable Tester, 2 AAA Batteries, Coax Terminator, Adapter Cables



# Southwire™

TOOLS & EQUIPMENT

[ BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK. ]

## 1-855-SWT00LS (855-798-6657)



Scan code to see more  
[Southwiretools.com](http://Southwiretools.com)