

High-Power LED PAR

LP16/6/40K/D-46

LED PAR16 Lamp



- Dimmable down to 5%*
- Advanced Optics & Thermal Management
- Ideal for track lighting
- Suitable for use in enclosed fixtures

Catalog Number	LP16/6/40K/D-46
Order Code	79678
UPC	751338005280
Wattage	6.5W
Input Voltage	120
Shape	PAR16
Base	E26 Medium
Beam Spread	40°
CRI	80
CCT	4000K
Initial Lumens	500
Average Rated Life	25,000
MOL	2.85"
Equivalent Wattage	60W
Warranty	5 years

Not for sale in California.

Specifications are subject to change without prior notice.

*Compatible with most leading edge or incandescent style dimmers



Revised July 2020