

Job Name/Title: _____ Catalog Number _____
 Contractor: _____ Notes: _____

LED A19 Series - JA8 Compliant

Dimmable LED GU24-Base

Features

- 85% energy savings compared to 60W incandescent
- Advanced optics and thermal construction
- Dimmable down to 10% of total light output*
- RoHS compliant and mercury free

Specs

- 120V
- >90 CRI
- 80 LPW
- 25,000 Average Rated Life
- -20°C Minimum start temperature

Applications

- Residential, decorative, task lighting, fan lights



GU24 Base



Catalog Number	Product Code	UPC Code	Color Temp	Beam Angle	Watts	Lumens	Equiv Wattage	ENERGY STAR	Case Qty
LA19/10/927/GU24D-46	70725	751338016477	2700K	220°	10	800	60W Incand. A19	Y	1/6/24
LA19/10/930/GU24D-46	70726	751338016484	3000K	220°	10	800	60W Incand. A19	Y	1/6/24
LA19/10/940/GU24D-46	70727	751338016880	4000K	220°	10	800	60W Incand. A19	-	1/6/24

Specifications are subject to change without prior notice.

Suitable for use in totally enclosed fixtures.

*Dimmable with standard LED rated dimmer such as Leviton DSL06, IPL06, or Lutron CL type dimmers

