

LED Wall Pack/Area Lamp

POWER & CCT SELECTABLE



SUGGESTED APPLICATIONS

- For use in wall pack retrofit applications, parking lot shoe box style luminaires, garages/canopies

FEATURES

- Choose wattage and color temperature at installation for up to nine possible configurations
- Ballast bypass operation¹ - no ballast or external driver required
- Internal thermal sensor reduces lamp power to 70% when operating in extreme high temperatures
- 350° rotatable base allows light to be aimed where it is needed most
- Base up/base down/horizontal operating positions
- Available in E26 and EX39 bases
- Support brace included



LED Wall Pack/Area Lamp POWER & CCT SELECTABLE

GENERAL SPECIFICATIONS

Input Voltage, Frequency: 120-277V, 60Hz
Power Factor, THD %: >0.9, <20%
Efficacy: 150 LPW
Functional Life (L70): 50,000 Hours
Minimum CRI: 85
Location Rating: Damp
Suitable for enclosed fixtures
Ambient Operating Temperature:
 Open fixture: -20°F to 140°F
 Enclosed fixture: -22°F to 113°F
Housing Construction: Aluminum heatsink



Power and CCT Temperature Selectable
(60W model shown)

ITEM SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	Max. Lamp Lumens	Max. Fixture Lumens	Wattage	Input Current @120/277V	CCT	Beam Angle	DLC ID [†]
LWP-20WPCTS-E26	73511	3,000	2,193	5W 10W 20W	0.18/0.08A	3000K 4000K 5000K	180°	-
LWP-20WPCTS-EX39	73512	3,000	2,193	5W 10W 20W	0.18/0.08A	3000K 4000K 5000K	180°	PIO1XWRH
LWP-30WPCTS-E26	73513	4,800	3,656	10W 20W 30W	0.25/0.11A	3000K 4000K 5000K	180°	-
LWP-30WPCTS-EX39	73514	4,800	3,656	10W 20W 30W	0.25/0.11A	3000K 4000K 5000K	180°	PLH4U545
LWP-40WPCTS-EX39	73515	6,200	4,564	20W 30W 40W	0.34/0.15A	3000K 4000K 5000K	180°	PQAL5NS3
LWP-60WPCTS-EX39	73516	9,600	6,454	20W 40W 60W	0.5A/0.22A	3000K 4000K 5000K	180°	PWT3GD4U

NOMENCLATURE

L-WP = LED Wall Pack - **20W** = 5/10/20 Watts **PCTS** = Power and CCT Select / **E26** = E26 Medium Base
30W = 10/20/30 Watts / **EX39** = EX39 Mogul Base
40W = 20/30/40 Watts
60W = 20/40/60 Watts

ACCESSORIES (SOLD SEPARATELY)

Catalog Number	Order Code	Description
WD-SP	79200	External surge protector, 10kA

NOTES:

[†]DLC Primary Use Designation: Outdoor Full-Cutoff Wall-Mounted Area Luminaires
[‡]When installing Topaz LED post top lamps in an HID fixture, ballast must be bypassed when present.
[§]Must meet minimum compartment size requirements to be suitable for enclosed fixtures
 This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.
 Specifications subject to change without prior notice. Replacement wattage shown depends on application and fixture.

Rev. 0, 01/22

LED Wall Pack/Area Lamp

POWER & CCT SELECTABLE

ENERGY SAVINGS

Catalog Number	LED Wattage	HID System Wattage	Watts Saved	Yearly Savings	5 Year Savings
Based on 12 hours/day and \$0.11/kWh					
LWP-20WPCTS-xx	20W	175W	155W	\$75	\$373
LWP-30WPCTS-xx	30W	250W	220W	\$106	\$530
LWP-40WPCTS-EX39	40W	320W	280W	\$135	\$675
LWP-60WPCTS-EX39	60W	400W	340W	\$164	\$819

DIMENSIONS / WEIGHTS

Catalog Number	(A)	(B)	Weight	Minimum Compartment Size ²
LWP-20WPCTS-E26	5.4"	3.6"	1 Lb.	6" x 6"
LWP-20WPCTS-EX39	5.4"	3.6"	1.1 Lbs.	6" x 6"
LWP-30WPCTS-E26	7"	3.6"	1.4 Lbs.	7.87" x 7.87"
LWP-30WPCTS-EX39	7"	3.6"	1.5 Lbs.	7.87" x 7.87"
LWP-40WPCTS-EX39	8.4"	3.6"	1.7 Lbs.	7.87" x 7.87"
LWP-60WPCTS-EX39	10.6"	3.6"	2.3 Lbs.	7.87" x 7.87"

