

## ALUMINUM GANTRIES

### STANDARD FEATURES

- Light weight
- Extremely portable
- Minimum parts
- Quick height adjustment
- Quick set up & tear down
- Adjustable span
- Anodized finished
- Pinch point free

### GH3/4T & GH2T FEATURES INOVATIVE MAST HEIGHT ADJUSTMENT

- Adjust mast lifting handle with plunger pin to comfortable lifting position
- Lift mast and remove quick-action mast locking pin
- A-frame legs lock in closed position – no bolts
- Push button leg lock release & locking
- A-frame legs lock in closed or opened position
- No pinch points – spacer prevents pinched fingers
- Tool-free a-frame operationg with instructions tube
- Casters can be locked in 90° angle for easy transport
- 8" caster with foot brake & four 90° locking positions
- Optional 10" flat free, double-wheel caster has both position and wheels lock. (Available on GH3/4T only)
- GH2T beam span adjustment on 10' (3 m) lengths & longer



## ALUMINUM GANTRIES

### GH5T FEATURES

- All aluminum
- 5 metric ton (11,000 lbs)
- Push button a-frame leg lock & release
- Built-in mast winch
- Caster with wheel & swivel lock
- Built-in mast winch raises and lowers beam with ease and mast locking pin sets mast with no bolts
- Folding third mast leg makes moving a-frame effortless
- The GH5T comes with chain & ratchet to pull a-frame legs together
- Ratchet 1st a-frame bolt to beam
- Ratchet 2nd a-frame until it can be pushed into place



ITEM #	DESCRIPTION	MODEL #	UPC	LOAD CAPACITY
785805	GH5T-15 with 15 ft. Beam	GH2T-15x15	661165858051	5 TON
785806	GH5T-12 with 12 ft. Beam	GH2T-12X12	661165858068	5 TON
785807	GH5T-10 with 10 ft. Beam	GH2T-10x10	661165858075	5 TON
OPTIONAL GH5T GANTRY ACCESSORIES				
785815	GH5T 15 ft. Beam Only	5TBEAM15	661165858150	-
785816	GH5T 12 ft. Beam Only	5TBEAM12	661165858167	-
785817	GH5T 10 ft. Beam Only	5TBEAM10	661165858174	-
785895	GH5T Trolley Assembly	GH5TROL	661165858952	-