



Southwire™

TOOLS & EQUIPMENT

DIAGONAL CUTTING PLIERS

The high leverage design of these diagonal cutting pliers provides cutting power while the hot riveted joint ensures smooth action and sturdy cuts.



SUPERIOR CUTTING POWER
INDUCTION HARDENED
CUTTING BLADES ENSURE LONG
LASTING CUTTING SURFACES

EFFECTIVELY CUTS MOST
HARDENED WIRE, ACSR, AND
SMALL BOLTS

SMOOTH ACTION
HOT RIVETED PIVOT JOINT FOR
SMOOTH ACTION AND STURDY
CUTS

HIGH LEVERAGE DESIGN
PROVIDES MAXIMUM CUTTING
POWER

COMFORTABLE GRIPS
AVAILABLE IN DUAL MOLDED
COMFORT GRIPS AND PLASTIC
DIPPED HANDLES

DURABLE
DROP FORGED CRV STEEL FOR
DURABILITY



AVAILABILITY

DIAGONAL CUTTING PLIERS



DCP8



DCP8D



DCPA8



DCPA8D



DCP6D

SPECIFICATIONS

MODEL #	DCP8D	DCPA8D	DCP8	DCPA8	DCP6D
STOCK #	582894	582895	589933	589932	58739601
DESCRIPTION	8" High Leverage Diagonal Cut Pliers Head Dip Handle	8" High Leverage Diagonal Cut Plier Angle Head Dip Handle	8" High Leverage Diagonal Pliers	8" High Leverage Diagonal Pliers Angle Head	6" High Leverage Diagonal Cut Pliers Dip Handle
HEIGHT	8"	8"	8"	8"	6"
WIDTH	2"	2"	2"	2"	2"
DEPTH	0.63"	0.63"	0.75"	0.75"	0.63"
WEIGHT	10 oz	10 oz	11 oz	11 oz	10 oz
HEAD TYPE	Standard	Angled	Standard	Angled	Standard
HANDLE COLOR	Yellow	Yellow	Yellow/Black	Yellow/Black	Yellow
HANDLE FINISH	Dipped Grip	Dipped Grip	Comfort Grip	Comfort Grip	Dipped Grip

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-SWTOOLS | 1-855-798-6657 | SOUTHWIRETOOLS.COM