



MAX PUNCH® XD

Heavy duty knockout punch driver for stainless and mild steel.

Features & Benefits:

- An advanced knockout tool used with a cordless drill to draw punch dies together for quick accurate knockouts
- No hydraulics, no ratcheting, no mess
- Thread-in/thread-out removable drawstuds (universal to fit most common KO dies)
- Rated to cut 10 gauge mild and stainless steel up to 4"
- Minimum drill recommendations: 18v cordless, equivalent of 550 in. lbs. torque rated
- Field Serviceable input shaft and internal drawstud.

REMOVABLE DRAWSTUDS FIT MOST INDUSTRY STANDARD KO DIES

NO HYDRAULICS, NO RATCHETING, NO MESS: AN ADVANCED KNOCKOUT TOOL USED WITH A CORDLESS DRILL TO DRAW PUNCH DIES TOGETHER FOR QUICK ACCURATE KNOCKOUTS

HEAVY DUTY



MODEL #	STOCK#	DESCRIPTION	HEIGHT	WIDTH	DEPTH	WEIGHT
MP-XD	63159701	MAX PUNCH® XD - Drive Unit only (no case)	5"	11.5"	4.25"	5.5lbs
MP-03PRO	57177201	Large Die Set for Stainless Steel (2 1/2" - 4") - in 1 case (Drive Unit not included)	16.5"	13"	11"	24 lbs
MPXD-SD	63159901	MAX PUNCH® XD w/stainless steel rated dies - 1/2" - 2" set (1 case)	16.5"	8.5"	13"	14.5lbs

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2019 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.