

24 AWG /4 Pair CAT5e Cable

60°C, 300V DIRECT BURIAL ; 4 UNSHIELDED TWISTED PAIR S

CONSTRUCTION:

- 1. **Conductors:** 24 AWG SOLID BARE COPPER
- 2. **Insulation:** PE BLUE & WHITE/BLUE STRIPE; ORANGE & WHITE/ORANGE STRIPE; GREEN & WHITE/GREEN STRIPE; BROWN & WHITE/BROWN
- 3. **Assembly:** 4 PAIRS INDIVIDUALLY TWISTED, CABLED; UNSHIELDED; AND JACKETED
- 4. **Jacket:** Polyethylene, Color : Black

APPLICATIONS AND FEATURES:

Southwire Cat 5e unshielded twisted pair cable is a high performance data communication cable. This cable is designed for outdoor direct burial network installations. Used in ethernet networking system, broadband and other multimedia voice applications.

SPECIFICATIONS:

- Meets or exceeds TIA/EIA 568-C.2
- DIR BUR
- RoHS-2 (European Directive 2011/65/EU)

SAMPLE PRINT LEGEND:

SOUTHWIRE 96294 CAT 5E 24/4PR DIRECT BURIAL – Z/YY (XXXX) - NNNNNN

PACKAGING

Standard lengths 1000 FT. Consult factory for other jacket colors and packaging options.

TABLE 1 - Product Electrical Characteristics

Stock Code	Max Capacitance (nF/100m @ 1 kHz) (AWG)	Max DC Resistance (Ω/100m @ 68°F)	Max Delay Skew (ns/100m)	Nom Velocity of Propagation (%)	Characteristic Impedance (Ω @ 1-100 MHz)	Nominal OD (Inchs)	Nominal OD (mm)	Nominal Weight (Lbs/Mft)	Nominal Weight (kg/km)
96294	5.6	9.38	45.0	68.0	100 +/- 15%	0.220	5.588	30.0	44.6

Freq (MHz)	Max Insertion Loss (dB/100m)	Min NEXT Loss (dB)	Min PSNEXT Loss (dB)	Min ACR (dB/100m)	Min PSACR (dB/100m)	Min ELFEXT (dB/100m)	Min PSELFEXT (dB/100m)	Min Return Loss (dB)
1	2.0	65.3	62.3	63.3	60.3	63.8	60.8	20
10	6.5	50.3	47.3	43.8	40.8	43.8	40.8	25
16	8.2	47.3	44.3	39.1	36.1	39.7	36.7	25
20	9.3	45.8	42.8	36.5	33.5	37.7	34.7	25
31.25	11.7	42.9	39.9	31.2	28.2	33.9	30.9	23.6
62.5	17.0	38.4	35.4	21.4	18.4	27.8	24.8	21.5
100	22.0	35.3	32.3	13.3	10.3	23.8	20.8	20.1

All dimensions are nominal and subject to nominal manufacturing tolerances. The customer will accept all factory lengths and +/- 10 percent of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. Since conditions of use are beyond Southwire's control all product data presented is for informational purposes only and does not create a binding obligation or liability on Southwire or confer any rights on any customer. The sale of products(s) is conditioned upon acceptance of a purchase order subject to Southwire's standard terms and conditions contained therein, including without limitation Southwire's standard warranty. Southwire disclaims all liability in connection with the use of information contained herein or otherwise.

Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com

Copyright © 2023 Southwire Company, LLC. All Rights Reserved

