SERIES 2100 CONTRACTOR LIFT



A Versatile, Inexpensive Contractor Lift

Series 2100 Features:

- Lifts 650 lb (300 kg)
- 12, 18 and 24 foot heights (3.9, 5.6 and 7.2 m)
- Lightweight
- All the features of the Series 2000 lift at a lower price!

Pulley Guards

Load cable <u>cannot</u> come off.



Reversible Forks

Using plunger pins, forks remove and reverse easily for added height or to get flush with a ceiling. No loose pieces!

DO NOT

Loading Bar

Great for overhead cranes

Roller Wheels

Helps to roll into trucks or vans

Inside-Mast Cable Feed

Cable feeds inside mast, removing exposed cable from near the operator's face.

Sumner-built Winch

Highly reliable, single-speed winch uses idler roller to feed cable evenly on the drum to avoid cable flats. Handles are removable when not in use.

Œ

10" Rough Terrain Wheels

Makes loading a truck or van hassle free.

Lockable 5"

Hard tread urethane wheels with Delrin® bearings.

Fast Action Stabilizer Legs

Mounted on base top, stabilizer legs fold down with ease and lock in place. Optional on model 2112.

		Max Height		Lifting Capacity		Lift Weight		Shipping Weight	
Part #	Description	Feet	Meter	lbs	kg	lbs	kg	lbs	kg
783650	2112 Contractor Lift	12' 11-3/8"	3.9	650	300.0	252	114.5	287	130.5
783651	2118 Contractor Lift	18' 4-3/8"	5.6	650	300.0	321	145.9	356	161.8
783652	2124 Contractor Lift	23' 9-3/8"	7.2	650	300.0	366	166.0	399	181.4









One piece slide-lock mechanism releases with plunger pins to fold legs. Leg rollers allow lift to be wheeled around with legs in stored position.

Optional Features for Sumner* 2100 Lifts



Boom Carriage (Part # 783642)

Ideal for installing pipe or lifting "from the top" applications. Uses four attaching plunger pins and has a 40" (100 cm) reach. Hook has five locations with load capacities of: 650 lbs (300 kg), 525 lbs (240 kg) 425 lbs (195 kg), 300 lbs (135 kg) 200 lbs (90 kg)



Fork Extensions (Part # 783691)

With the push of a button, forks may be extended from 28" to 42" (71–106 cm). With longer forks, the weight capacity decreases to 200 lbs (90 kg) and is clearly displayed on the forks when extended. A second button returns the extension for convenient storage inside the forks.



Pipe Cradle (Part # 783705)

Great for duct pipe or other HVAC applications. Slides over standard forks. Packaged in sets of two.



Steering Handle (Part # 786695)

Optional steering handle improves maneuverability of lift. With a push of a release button, handle folds out of the operator's way.



Two Speed Winch Handle Kit (Factory Installed Part # 783765)

The two speed winch handle offers a standard speed setting or a high speed setting for quickly positioning forks in half the time. Available only on Series 2100 lifts commencing with serial number 9433. For field installation kit, use part #783761.

Safety Brake

Each mast and carriage can have a factory installed, gravity actuated safety brake which holds loads in place to help avoid any slack in the cable.

Part #	Description
783882	Safety brake - 2112
783883	Safety brake - 2118
783884	Safety brake - 2124

Series 2100 Contractor Lift Dimensions	2112		2118		2124	
Height - stowed	84"	2.13 m	84"	2.13 m	84"	2.13 m
Length - stowed	34"	0.86 m	34"	0.86 m	34"	0.86 m
Height - operating	84"	2.13 m	84"	2.13 m	84"	2.13 m
Length - operating	62"	1.57 m	73"	1.84 m	73"	1.84 m
Base width	31-1/4"	0.80 m	31-1/4"	0.80 m	31-1/4"	0.80 m
Width with stabilizer legs	74"	1.88 m	74"	1.88 m	74"	1.88 m
Ground clearance	2-1/2"	6.4 cm	2-1/2"	6.4 cm	2-1/2"	6.4 cm
Load height (minimum)	6"	15.2 cm	6"	15.2 cm	6"	15.2 cm
Maximum height (forks down)	10' 11-5/8"	3.3 m	16' 4-5/8"	5.0 m	21' 9-5/8"	6.6 m
Maximum height (forks reversed)	12' 11-3/8"	3.9 m	18' 4-3/8"	5.6 m	23' 9-3/8"	7.2 m