

Job Name/Title:_____Catalog Number_____ Contractor:____

____Notes:_

LED Surface Mount Disk Light WITH INTEGRATED MOTION SENSOR





Effortless and Efficient Lighting with Motion Sensor Convenience

The Topaz 6" Surface Mount Disk Light with built-in motion sensor and automatic time-out adds hands-free, quality LED lighting to storage spaces, utility rooms, pantries, and closets. Whether ceiling or surface mounted, the Surface Mount Disk Light installs easily and fits standard 4" junction boxes. Two models are available, 3000K and 4000K CCT, and both are ENERGY STAR® certified with efficacy up to 71 LPW.

FEATURES

- Integrated PIR motion sensor with 16' diameter detection range
- 10-minute automatic time out when motion is not detected¹
- Polycarbonate lens with uniform, wide beam distribution
- Includes 360° rotatable mounting bracket to allow optimal sensor positioning*
- T24 JA8: Can be used to comply with California Energy Commission's High Efficacy LED light source requirements

SUGGESTED APPLICATIONS

- Commercial and residential
- Multi-family, hospitality, hallways, living rooms, storage areas, pantries and utility rooms
- Suitable for use in closets when installed in accordance with NFPA 70, NEC section 410.16 (A)(3) and 410.16 (C)(5)





LED Surface Mount Disk Light WITH INTEGRATED MOTION SENSOR

GENERAL SPECIFICATIONS

Input Voltage, Frequency: 120V, 60Hz **Power Factor: >**0.9 Efficacy: 71 LPW Minimum CRI: 90 Beam Angle: 100° Functional Life (L70): 50,000 hours Location Rating: Wet Ambient Operating Temperature: -4°F to 104°F





Α

ITEM SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	Lumens	Wattage	Input Current	сст	Size	ENERGY STAR®
SDL6-14W-30K-WH-MS	73329	990	14W	125mA	3000K	6"	Y
SDL6-14W-40K-WH-MS	73330	1,000	14W	125mA	4000K	6"	Y

NOMENCLATURE

SDL6 = 6" Surface Mount Disk LED - 14W = 14W - 30K = 3000K - WH = White - MS = Motion Sensor **40K** = 4000K

Contractor:

ENERGY SAVINGS

Catalog Number	LED Wattage	Incandescent Replacement Wattage	Watts Saved	Yearly Savings	5 Year Savings
Based on 12 hours/day and \$0.11/kWh					
SDL6-14W-xxK-WH-MS	14W	75W	61W	\$30	\$150

DIMENSIONS / WEIGHTS



NOTES:

*Approximation based on positioning of fixture on mounting bracket.

¹The 10-minute timeout is factory preset with no manual override option.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Specifications subject to change without prior notice. Replacement wattage shown depends on application and fixture.

WARNING: Some products included in this specification sheet may be subject to the warning requirements of California's Proposition 65. Please refer to product packaging for more information.