



# Southwire™

## SIMpull™ FLEXIBLE METAL LEADER FISH TAPE

### FLEXIBLE METAL LEADER

Easily glides through conduit bends and around existing wire

### IMPACT RESISTANT CASE

Certified Drop Rating of 15 Feet

### LASER ETCHED FOOT MARKINGS

Identify conduit run lengths with incremental foot markings

### ADVANCED TAPE GUIDE

Improved housing mechanics for smoother payout & reel-in

### IMPROVED PUSH

5.5mm tape works well in conduit up to 3 inches  
4.5mm tape works well in conduit up to 2 inches



SCAN TO SEE MORE



MODEL #	STOCK #	UPC #	DESCRIPTION	HEIGHT	WIDTH	DEPTH	WEIGHT
FTSP55-125FML	67015240	032886751202	SIMpull™ Flexible Metal Leader 5.5mm 125'	16"	12"	2"	2.5 lbs
FTSP45-125FML	59896940	032886961823	SIMpull™ Flexible Metal Leader 4.5mm 125'	16"	12"	2"	2.5 lbs
FTSP45-75FML	59897040	032886961830	SIMpull™ Flexible Metal Leader 4.5mm 75'	16"	12"	1.5"	2.0 lbs
FTSP4.5FML-LRKIT	64277640	032886985942	SIMpull™ Replacement Leader Kit, 2x of each Leader Included 4.5mm	6"	17"	4"	2.6 lbs
FTSP3.0FML-LRKIT	64277940	032886985966	SIMpull™ Replacement Leader Kit, 2x of each Leader Included 3.0mm	6"	17"	4"	2.6 lbs

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2021 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.