



Southwire™

TOOLS & EQUIPMENT

PROLIGHT™

SLIM SERIES

**LONG LASTING
LED**

The Southwire ProLight Slim Series work lights bring value and versatility to the jobsite. The 11 available configurations allow Pros to select the light that's right for their application including single head with floor stand or tripod, dual head with tripod, or single head with magnet. When it comes to performance, the Slim Series will not disappoint, delivering between 1500 and 5000 lumens of 5000K light per head. Additionally, these lights are rated IP65 for indoor or outdoor use, will last for 50,000 hours, and can operate in ambient temperatures between -40° and 122°F.

- Compact design improves portability and makes the lights easier to store
- Over-optic design provides a powerful and smooth light distribution
- IP65 rated for indoor and outdoor use
- 5000K CCT LEDs have a rated life of 50,000 hours
- Temperature rating: -40 to 122°F
- Available in 11 configurations including magnetic mounting options



411215

- 1500 lumens
- 15 Watts
- Single head with tripod included, extends up to 5 feet high
- 5 foot 18/3 cord



411315

- 3000 lumens total
- 30 Watts
- Dual head with tripod included, extends up to 5 feet high
- 5 foot 18/3 cord plus splitter



411015

- 1500 lumens
- 15 Watts
- Floor stand provided
- 5 foot 18/3 cord

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



411230

- 3000 lumens
- 30 Watts
- Tripod included, extends up to 5 feet high
- 5 foot 18/3 cord



411030

- 3000 lumens
- 30 Watts
- Floor stand provided
- 5 foot 18/3 cord



411330

- 6000 lumens total
- 60 Watts
- Tripod included, extends up to 5 feet high
- 5 foot 18/3 cord plus splitter



411430

- 3000 lumens
- 30 Watts
- Floor stand and magnet provided
- 5 foot 18/3 cord



411250

- 5000 lumens
- 50 Watts
- Tripod included, extends up to 5 feet high
- 5 foot 18/3 cord



411050

- 5000 lumens
- 50 Watts
- Floor stand provided
- 5 foot 18/3 cord



411350

- 10,000 lumens
- 100 Watts
- Tripod included, extends up to 5 feet high
- 5 foot 18/3 cord plus splitter



411450

- 5000 lumens
- 50 Watts
- Floor stand and magnet provided
- 5 foot 18/3 cord

BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

TOOLS & EQUIPMENT



SLIM SERIES

Item #	Description	Item Length	Item Height	Item Width	Mast Pack QTY	Lumens	UPC
411015	ProLight™ Slim Series 15-Watt LED Work Light - Single Head w/ Floor Stand	11	8	11	8	1500	786625410157
411215	ProLight™ Slim Series 15-Watt LED Work Light - Single Head w/ Standard Tripod	35	69	35	1	1500	786625000068
411315	ProLight™ Slim Series 15-Watt LED Work Light - Twin Head w/ 2-Step Tripod	35	69	35	1	3000	786625000075
411030	ProLight™ Slim Series 30-Watt LED Work Light - Single Head w/ Floor Stand	7.5	6.5	9	4	3000	786625411031
411230	ProLight™ Slim Series 30-Watt LED Work Light - Single Head w/ 2-Step Tripod	35	70.5	35	1	3000	786625000082
411330	ProLight™ Slim Series 30-Watt LED Work Light - Twin Head w/ 2-Step Tripod	38	70.5	38	1	6000	786625000099
411430	ProLight™ Slim Series 30-Watt LED Work Light - Single Head w/ Magnet	8.625	10.5	8.625	1	3000	786625000365
411050	ProLight™ Slim Series 50-Watt LED Work Light - Single Head w/ Floor Stand	7.5	8	10.58	4	5000	786625410508
411250	ProLight™ Slim Series 50-Watt LED Work Light - Single Head w/ 2-Step Tripod	32	71.75	32	1	5000	786625000105
411350	ProLight™ Slim Series 50-Watt LED Work Light - Dual Head w/ 2-Step Tripod	35	71.5	35	1	10000	786625000372
411450	ProLight™ Slim Series 50-Watt LED Work Light - Single Head w/ Magnet	10.375	11.5	10.375	1	5000	786625000389



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2018 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.