

TROLLEY

STANDARD FEATURES

- Light Weight Robust Construction
- Trolley Opening Adjust For Narrow to Wide Range of Beams
- Works with Most Brands of Chain Hoist
- Ideal for Temporary or Semi-Permanent Hoist Anchor Points
- Powder Coated for Excellent Corrosion Protection
- Ideal for Industrial and Construction Lifting Applications
- Available in 6 Sizes (1/2 -Ton, 1-Ton, 2-Ton, 3-Ton, 5-Ton, 10-Ton)
- Complies with ASME B30.11, B30.16, B30.17, B30.21 Requirements
- Load Tested to 150% of Rated Capacity
- Precision Ball Bearings Wheels for Smooth Operation



CERTIFICATIONS

- EN13157
- EN818-7
- Machine Directive 2006/42/EC

PART #	STOCK #	UPC	DESCRIPTION	HEIGHT	WIDTH	DEPTH	WEIGHT
MT050C	787586	661165875867	1/2-TON MANUAL TROLLEY	6.10"	9.06"	8.58"	15.62lbs
MT100C	787587	661165875874	1-TON MANUAL TROLLEY	7.12"	11.65"	10.11"	28.16lbs
MT200C	787588	661154875881	2-TON MANUAL TROLLEY	8.44"	12.32"	11.81"	41.36lbs
MT300C	787589	661165875898	3-TON MANUAL TROLLEY	9.92"	13.14"	13.38"	74.14lbs
MT500C	787590	661165875904	5-TON MANUAL TROLLEY	11.41"	14.29"	14.96"	111.54lbs
MT1KC	787591	661165875911	10-TON MANUAL TROLLEY	14.35"	16.14"	15.31"	193.61lbs