



Southwire™

BX, FLEX, SNAP-IN CONNECTORS

SET SCREW TYPE - STRAIGHT

FEATURES

- Easy to install
- Labor savings by simply snap the fitting into the knockout hole
- Snap-In design
- Set screw type
- Not suitable for PVC jacketed/coated cables
- Wide variety of cables

APPLICATION

- Indoor use only
- In a dry location
- Use to connect steel to a steel outlet box or other metal enclosure

STANDARD MATERIAL

- Zinc die cast

CERTIFICATIONS

- cULus



130STSW



APPROVED CABLES

CABLE TYPE	CONDUIT, SIZE/ CABLE, AWG	CABLE DIAMETER RANGE (IN)
AC CABLE, ALUMINUM	14/2 – 10/3	0.445 – 0.630
AC CABLE, STEEL	14/2 – 10/3	0.451 – 0.593
METAL CLAD CABLE, MCI-A, STEEL	14/2 – 10/3	0.451 – 0.593
METAL CLAD CABLE, MCI-A, ALUMINUM	14/2 – 10/3	0.439 – 0.58
FMC, STEEL	3/8"	0.56 – 0.61
FMC, ALUMINUM	3/8"	0.56 – 0.61
RWFMC, STEEL	3/8"	0.56 – 0.61
RWFMC, ALUMINUM	3/8"	0.56 – 0.61
METAL CLAD CABLE, MCC, ALUMINUM	14/2 – 10/3	0.451 – 0.593



PART #	SIZE	KO	INNER QTY.	MASTER QTY.	WEIGHT/CASE (LBS.)	HEIGHT	WIDTH	LENGTH
130STSW	3/8"	1/2"	20	200	1	0.94"	0.94"	1.12"

Rev. 0, 01/25

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2025 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.