



Southwire™

TOOLS & EQUIPMENT



NEW HAND TOOLS & ACCESSORIES

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2019 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



ELECTRICIAN'S HAMMERS

Southwire now carries two new Electrician's Hammers that will become your new jobsite go-to! Our 18 oz. Electrician's Hammer is specifically designed to easily remove Romex™ Brand Wire Staples while our 20 oz. delivers the same great quality, made with heavy duty drop forged steel! Both feature Southwire's Lifetime, No-Hassle tool warranty.

ELECTRICIAN'S HAMMER 18 oz.

- Romex™ Brand Wire Staple remover allows for easy removal of staples
- 18 oz. head constructed of heavy duty drop forged steel
- Extended neck designed for easy reach into outlet boxes
- High strength, comfort grip fiberglass handle for vibration resistance

ELECTRICIAN'S HAMMER 20 oz.

- 20 oz. head constructed of heavy duty drop forged steel
- Smooth face leaves fewer marks on striking surfaces
- High strength, comfort grip fiberglass handle for vibration resistance

Model #	UPC	Description	Master Pack Qty
BMEH18	032886711466	ELECTRICIAN'S HAMMER 18 OZ. (TRI)	2
BMEH20	032886711473	ELECTRICIAN'S HAMMER 20 OZ. (TRI)	2



BMEH18

BMEH20

CELL PHONE POUCHES

Step-up your efficiency by adding a Southwire cell phone pouch to your belt! This handy case comes with a magnetic flap, card holder and bottle opener for when it's time to play just as hard as you've worked. Both come with a two year warranty.

LARGE & STANDARD PHONE POUCH

- Fits standard and Plus size mobile devices
- Magnetic flap provides secure closure
- Front pocket ideal for storing business or bank cards
- Bottle opener included
- Rotatable belt clip provided for carrying convenience

Model #	UPC	Description	Master Pack Qty
CPCH-ST	032886715891	STANDARD CELL POUCH	4
CPCH-PLUS	032886715907	PLUS CELL POUCH	4



CPCH-ST

CPCH-PLUS



THERMOMETERS & DRIVERS

IR THERMOMETERS

Southwire's new IR Thermometers are designed for the professional because they're easy-to-use and built tough. You'll like the large, uncluttered LCD display that makes temperature readings fast & easy. Viewing and changing advanced features is also a snap. Both thermometers are built to withstand a 6.5 foot drop and they're backed with a 5-year, no-hassle warranty.



31212S 930°F 12:1 INFRARED THERMOMETER WITH DUAL LASER TARGETING

- Dual laser targeting for precise aiming
- 12:1 Optics for extra long-distance accuracy
- Adjustable Emissivity - higher accuracy when measuring different materials
- Continuous Measurement – built-in tripod mount and Lock mode
- Protective carrying pouch included and lanyard attachment
- Large LCD screen and easy to navigate feature menu

31011F 750°F 10:1 INFRARED THERMOMETER

- Simple and Economical
- Single Laser targeting
- 10:1 Optics for long distance accuracy
- Fixed emissivity



31212S



31011F

Model #	UPC	Description	Master Pack Qty
31212S	032886710285	930°F Infrared Thermometer Dual Laser Targeting	2
31011F	032886710278	750°F 10:1 Infrared Thermometer	2

STUBBY NUT DRIVER

If you love our stubby drivers, give our 5-IN-1 Stubby Nut Driver a try! Delivering maximum torque, 5 nut driver bit sizes and an easy way to get into tight spots, this tool will become a new jobsite essential!



5-IN-1 STUBBY NUT DRIVER

- Come with 3/16", 1/4", 5/16", 3/8", and 1/2" nut driver sizes
- Cushion grip handle provides extra comfort and maximum torque
- Chrome plated finish for corrosion resistance
- Hollow shafts for screw clearance



NDS5N1

Model #	UPC	Description	Master Pack Qty
NDS5N1	032886711459	5-IN-1 STUBBY NUT DRIVER(TRI)	3

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2019 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



VOLTAGE TESTERS



Southwire is proud to introduce a new line of voltage testers that will become an essential part of your test and measurement inventory. Southwire's new voltage testers perform three important tasks electrician's do on a regular basis: detect voltage, test voltage, and test continuity. You can't beat these new testers for value and safety. These testers are CAT IV 600V Safety Rated and rugged construction that withstands a 6.5 foot drop.

41151S COMPACT VOLTAGE & GFCI TESTER

- Easy-to-read LED display
- Tests GFCI outlets and circuits
- Measures AC voltage from 12 volts to 480 volts
- Measures DC voltage from 9 volts to 110 volts
- Accepts Southwire's magnetic strap sold separately



41151S

41161N VOLTAGE DETECTOR & TESTER

- Easy-to-read LED display
- Measures AC voltage from 12 volts to 600 volts
- Measures DC voltage from 9 volts to 400 volts
- Built-in non-contact voltage (NCV) detector that detects 100 volts to 1000 volts
- NCV has automatic self-test feature to ensure the NCV is working properly
- Tests continuity with visual and audible indication
- Bright LED worklight
- Accepts Southwire's magnetic strap (Model 60151R sold separately)



41161N

41171N PRECISION VOLTAGE DETECTOR & TESTER

- Large backlit LCD display
- Measures AC/DC voltage up to 600 volts
- Built-in non-contact voltage (NCV) detector that detects 100 volts to 1000 volts
- NCV has automatic self-test feature to ensure the NCV is working properly
- Tests continuity with visual and audible indication
- Bright LED worklight
- Accepts Southwire's magnetic strap (Model 60151R sold separately)



41171N

Model #	UPC	Description	Master Pack Qty
41151S	032886710292	41151S Compact Voltage & GFCI Tester	3
41161N	032886710308	41161N Voltage Detector & Tester	3
41171N	032886710315	41171N Precision Voltage Detector & Tester	2





Southwire™ | TOOLS & EQUIPMENT



GET SOCIAL WITH US:



/SOUTHWIRETOOLS
/SOUTHWIRETOOLSLATINO



@SOUTHWIRETOOLS



@SOUTHWIRETOOLS



SOUTHWIRETOOLS

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2019
Southwire Company, LLC. All rights reserved.