



# Southwire™

## FLEXIBLE LIQUIDTIGHT CONDUIT

### METALLIC - COIL

#### FEATURES

- Crush and corrosion resistant steel core for lasting mechanical protection
- Durable PVC jacket is oil, heat and sunlight resistant (UV)
- Smooth interior for easy wire pull through
- 3/8" thru 1-1/4" with continuous bonding strip

#### APPLICATION

- For use in damp or wet locations, suitable for commercial and industrial use
- Listed for direct burial and in poured concrete

#### STANDARD MATERIAL

- PVC jacketed steel core coil wrapped in clear plastic shrink wrap



6100UL



PART #	SIZE	FEET COIL	SHIP CASE	WEIGHT/ CASE (LBS.)	INSIDE DIAMETER		OUTSIDE DIAMETER		OUTSIDE DIAMETER PVC JACKET	
					MIN.	MAX.	MIN.	MAX.	MIN.	MAX.
6100UL	3/8"	100'	100'	25	.484"	.504"	.594"	.614"	.690"	.710"
6101UL	1/2"	100'	100'	29	.622"	.642"	.732"	.765"	.820"	.840"
6102UL	3/4"	100'	100'	41	.82"	.84"	.930"	.96"	1.03"	1.05"
6103UL	1"	100'	100'	55	1.04"	1.066"	1.201"	1.226"	1.29"	1.315"
6104UL	1-1/4"	50'	50'	33	1.38"	1.41"	1.54"	1.57"	1.63"	1.66"
6105UL	1-1/2"	50'	50'	54	1.575"	1.60"	1.735"	1.77"	1.865"	1.90"
6106UL	2"	25'	25'	32	2.02"	2.045"	2.18"	2.215"	2.34"	2.375"
6107UL	2-1/2"	25'	25'	46	2.48"	2.505"	2.64"	2.675"	2.84"	2.875"
6108UL	3"	25'	25'	56	3.07"	3.10"	3.295"	3.335"	3.46"	3.50"
6109UL	3-1/2"	25'	25'	69	3.50"	3.54"	3.72"	3.789"	3.96"	4"
6110UL	4"	25'	25'	80	4"	4.22"	4.22"	4.28"	4.46"	4.50"

Rev. 0, 01/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.