



Southwire™

SIMPush™ RIGID CONDUIT BODIES

C TYPE - ALUMINUM

FEATURES

- Gasket NBR Nitrile
- No need to thread conduit
- Works with threaded or non-threaded RMC, IMC, GRC, ARC and rigid stainless steel
- Copper free aluminum, powder coat
- Reusable, tested for up to 100 removal cycles
- Watertight, concrete tight, direct burial rated

APPLICATIONS

- Allows access for inspection, pulling and maintenance

STANDARD MATERIAL

- Copper free aluminum

CERTIFICATIONS

- UL Listed, 514B, IP66, NEMA 4X



R-CB-050

STOCK #	MODEL #	SIZE	QUANTITY PER BAG	OVERALL PRODUCT DIMENSIONS			ASSOCIATED REMOVAL TOOL MODEL #	REMOVAL TOOL INCLUDED
				HEIGHT	WEIGHT	LENGTH		
RETAIL POLY-BAG PACKAGING								
65082601	R-CB-050	1/2"	1	6.80"	1.31"	1.30"	R-RT-1P	---
65082701	R-CB-075	3/4"	1	7.56"	1.53"	1.499"	R-RT-1P	---
STOCK #	MODEL #	SIZE	QUANTITY PER BOX	HEIGHT	WEIGHT	LENGTH	ASSOCIATED REMOVAL TOOL MODEL #	REMOVAL TOOL INCLUDED
CONTRACTOR PACK								
65082602	R-CB-050W	1/2"	8	6.80"	1.31"	1.3"	R-RT-1P	---
65082702	R-CB-075W	3/4"	6	7.56"	1.53"	1.499"	R-RT-1P	---
65082802	R-CB-100W	1"	6	8.605"	1.74"	1.70"	R-RT-2P	---
65082902	R-CB-125W	1-1/4"	4	10.818"	2.49"	2.29"	R-RT-2P	---

Rev. 0, 06/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.