



# Southwire™

## SMARTLB™ CONDUIT BODIES

### ALUMINUM OR PVC

#### FEATURES

- For use with EMT, IMC, Rigid conduit or LT flexible conduit and fittings
- Suitable for indoor/outdoor (OSP) and plenum use
- Built in radius helps prevent cables from getting damaged
- Includes gasketed cover for wet locations
- Meets minimum bend radius of ANSI/TIA/EIA 568 & NECA/FOA
- Recommended by BICSI TDMM 13th for communication cable

#### APPLICATION

- For ease of Service Entrance wire

#### STANDARD MATERIAL

- Aluminum or PVC

#### STANDARD FINISH

- Powder coat (Aluminum)

#### CERTIFICATIONS

- CSA US Listed



KBLB120



PART #	MATERIAL TYPE	SIZE	MASTER QTY.
KBLB120	ALUMINUM	1-1/4"	20
KBLB250		2-1/2"	4
KBLB400		4"	2
KBLB121	PVC	1-1/4"	20
KBLB251		2-1/2"	4
KBLB401		4"	2

Rev. 0, 03/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.