



**Southwire™**

# SNAP-IN DUPLEX CONNECTOR

## 1 SCREW CLAMP TYPE

### FEATURES

- Easy to install
- Labor savings by simply snap the fitting into the knockout hole
- Snap-In design
- 1 Screw clamp type
- Not suitable for PVC jacketed/coated cables
- Wide variety of cables

### APPLICATION

- Indoor use only
- In a dry location
- Use to connect steel to a steel outlet box or other metal enclosure

### STANDARD MATERIAL

- Zinc die cast

### CERTIFICATIONS

- cULus



350STSW



## APPROVED CABLES

CABLE TYPE	CONDUIT, SIZE/ CABLE, AWG	CABLE DIAMETER RANGE (IN)
AC CABLE, ALUMINUM	14/2 – 10/3	0.445 – 0.610
AC CABLE, STEEL	14/2 – 10/3	0.451 – 0.593
METAL CLAD CABLE, MCI-A, STEEL	14/2 – 10/3	0.451 – 0.593
METAL CLAD CABLE, MCI-A, ALUMINUM	14/2 – 10/3	0.439 – 0.58
FMC, STEEL	3/8"	0.56 – 0.61
FMC, ALUMINUM	3/8"	0.56 – 0.61
RWPMC, STEEL	3/8"	0.56 – 0.61
RWPMC, ALUMINUM	3/8"	0.56 – 0.61
METAL CLAD CABLE, MCC, ALUMINUM	14/2 – 10/3	0.451 – 0.593

PART #	SIZE	KO	INNER QTY.	MASTER QTY.	WEIGHT/CASE (LBS.)	HEIGHT	WIDTH	LENGTH
350STSW	3/8"	1/2"	25	250	2.5	0.93"	1.63"	1.65"

Rev. 0, 01/25

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2025 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.