TRIGGERS® WIRELESS SAFETY SWITCH SYSTEM

Safety system is designed to control the input power of any piece of jobsite equipment.

Features & Benefits:

- Works with all brands of electrically driven equipment
- Saves time by avoiding unnecessary stops and restarts
- High visablity LED status lights
- Monitors amperage draw indicating when to switch puller to low speed
- Triggers® Wireless Safety Switch System is UL Listed and FCC Certified and carries an IP55 rating
- Foot controls contain dual redudant activation switches
- Military grade 6.8 amp hour lithium ion battery packs
- Stand Alone roller system for improved rope path



HANDHELD REMOTES CAN CONTROL PULL FROM ANY LOCATION

INTERGRATED HIGH EFFECIENCY CHARGING SYSTEM HOUSED WITHIN PRODUCT CASE

INCREASES SAFETY BY REDUCING ISSUES ASSOCIATED WITH AUDIO MISCOMMUNICATION

HIGH RANGE COMMUNICATES UP TO 1500' BETWEEN WALLS AND 3.7 MILES LINE OF SIGHT

FOOT SWITCHES WORK IN BOTH PAIRED MODE OR IN STANDALONE MODE WITH ANY ELECTRICALLY DRIVEN PIECE OF EQUIPMENT







949-833-3052









MODEL #	STOCK#	UPC #	DEPTH	WIDTH	HEIGHT	WEIGHT
TSS01	59713201	0-32886-95933-2	16.42"	21.50"	12.54"	30 lbs
DESCRIPTION		Triggers® Wireless Safety Switch System	SHIPPING		Вох	