



# FO32 ECO

## Reduced Wattage

### FO32/28W/841/XP-39

#### 28W T8 Fluorescent Lamp



- *TCLP Compliant*
- *Extra Long Life*
- *CEE Qualified*

<b>Item #</b>	FO32/28W/841/XP-39
<b>Product Code</b>	78327
<b>Watts</b>	28
<b>Lamp Shape</b>	T8 Linear
<b>Base</b>	G13 Bi-pin
<b>CRI</b>	82
<b>Color Temp</b>	4100K
<b>Initial Lumens</b>	2,700
<b>Average Rated Life</b>	30,000
<b>MOL</b>	48"

Specifications are subject to change without prior notice.

- \*36,000 hrs Rapid start ballast
- \*30,000 hrs Instant start ballast



[www.topaz-usa.com](http://www.topaz-usa.com)

**NY Office:** 925 Waverly Ave • Holtsville, NY 11742 • 800-666-2852 • Fax: 631-758-8026  
**CA Office:** 225 Parkside Drive, San Fernando, CA 91340 • 888-551-2852 or 818-838-3123 • Fax: 888-690-2852 or 818-838-3102  
**FL Office:** 2020 West 26th Street, Jacksonville, FL 32209 • 800-338-2852 • Fax: 772-778-5386