



Southwire™

ENT CONDUIT COILS

FEATURES

- Electrical Nonmetallic Tubing (ENT) coils
- UV rated
- Suitable for concrete encasement
- Pull resistant
- Fire resistant
- Impact resistant
- Flexible enough to be bent by hand, tough enough to withstand crushing and breaking

APPLICATION

- Can be installed and concealed in floors, walls and ceilings
- May be installed and exposed in areas not subject to physical damage and where the building does not exceed three floors above grade

STANDARD MATERIAL

- Heavy duty impact resistant PVC



1621



PART #	SIZE	FEET PER COIL	FEET PER PACK	WEIGHT/ CASE (LBS.)	INNER DIAMETER	OUTER DIAMETER
1621	1/2"	200	400	19	.578"	.84"
1622	3/4"	100	200	13	.778"	1.05"
1623	1"	100	100	17	1"	1.315"

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.