



Friendly Service... Powerful Solutions



LINEAR FLUORESCENT LAMPS

FP54/835/HO-39



Features

T5 High Output Fluorescent Tube, 3500K, 85 CRI, TCLP, ROHS Compliant, Made in China

Specifications

Item #	Watts	CCT (K)	CRI	Approx Lumens	Bulb Shape	Rated Life (HRS)	MOL (IN)	Diameter (IN)	Mercury Content (Mg)	Base
FP54/835/HO-39	54	3500	85	4700 Initial	T5 Linear Tube	24,000	45.8	0.625	3.5	G5 Miniature Bi-Pin

TOPAZ LIGHTING AND ELECTRIC / www.topaz-usa.com

NY Office: 925 Waverly Ave • Holtsville, NY 11742 • 800-666-2852 • Fax: 631-758-8026

CA Office: 225 Parkside Drive, San Fernando, CA 91340 • 888-551-2852 or 818-838-3123 • Fax: 888-690-2852 or 818-838-3102

FL Office: 2020 West 26th Street, Jacksonville, FL 32209 • 800-338-2852 • Fax: 772-778-5386