



T5 High Output Linear Fluorescent Lamp

FP24/835/HO



TCLP Compliant, RoHS Compliant

Specifications

Item #	Watts	CRI	CCT (K)	Initial Lumens	Bulb Shape	Rated Life (HRS)	MOL (IN)	Base
FP24/835/HO-39	24	85	3500	1750	T5 Linear Tube	24,000	24	G5 Min

Specifications are subject to change without prior notice. For technical questions about these products, call 888.551.2852 x1451.



www.topaz-usa.com

NY Office: 925 Waverly Ave • Holtsville, NY 11742 • 800-666-2852 • Fax: 631-758-8026
CA Office: 225 Parkside Drive, San Fernando, CA 91340 • 888-551-2852 or 818-838-3123 • Fax: 888-690-2852 or 818-838-3102
FL Office: 2020 West 26th Street, Jacksonville, FL 32209 • 800-338-2852 • Fax: 772-778-5386