




PRODUCT SPECIFICATION

CATALOG NUMBER: See table below
DESCRIPTION: Extension cord with power indicator light in the cord connector
APPROVALS: UL Listed and CSA Certified or CUL Listed Outdoor Use Cord Set

CONSTRUCTION PARAMETERS:

Cable type: SJTW, see table below for gauge
 Cable jacket material: PVC, see table below for color
 Cord rating: Hard, Usage per the National Electrical Code
 Cable legend type: Indent print



Note: Plug style may vary

Attachment plug configuration: NEMA 5-15P
 Cord connector configuration: NEMA 5-15R
 Plug and connector material: Clear PVC, with neon power indicator lamp in the connector

ELECTRICAL AND ENVIRONMENTAL PROPERTIES:

Cable temperature rating: -40 to +60 C
 Nominal operating voltage: 125 VAC
 Maximum operating current: See table below

Catalog No.	Gauge	Color	Length	Current Rating	Case QTY	UPC
2588SW0002	12/3	Yellow	50 ft	15A	6	029892115043
2589SW0002		Yellow	100 ft		4	029892825898



This product complies with European Directive 2011/65/EU (RoHS-2)

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part.

We disclaim all liability in connection with the use of information contained herein or otherwise.

This specification is the proprietary intellectual property of Southwire Company LLC. Any information contained herein shall not be disclosed to any party without the written consent of Southwire Company LLC.

