

RECHARGEABLE WORKLIGHTS



RECHARGEABLE HANDHELD LIGHTS

- Smooth dimming feature by holding down the power button
- Mountable magnetic base
- Built-in hanging hook
- Lithium-ion battery charges via mini DC
- 6000K color temperature



HHL1030R 300 LUMEN RECHARGEABLE HANDHELD LIGHT

- 300 30 lumen output
- Up to 10 hours of runtime
- IP54/IK07 rated
- Drop tested to 2 meters



HHL1040R 400 LUMEN RECHARGEABLE HANDHELD LIGHT

- 400 40 lumen flood light
- 80 lumen spot light
- Up to 10 hours of runtime
- Battery indicator display
- IP20 rated
- Drop tested to 1 meter



HHL1060R 600 LUMEN RECHARGEABLE HANDHELD LIGHT

- 600 60 lumen flood light
- 150 lumen spot light
- Up to 15 hours of runtime
- Battery indicator display
- IP54/IK07 rated
- Drop tested to 1.5 meters

RECHARGEABLE WORKLIGHT

WL1010R 1000 LUMEN RECHARGEABLE WORK LIGHT

- High and low lumen output levels
- Auxiliary USB output to charge other devices
- Up to 6 hours of runtime
- IP65 rated for outdoor use
- Swivel kickstand
- Lithium-ion battery charges via micro-USB
- 6500K color temperature



RECHARGEABLE CLAMPING WORKLIGHT

CL1170R

1700 LUMEN RECHARGEABLE WORK LIGHT

- Clamping base
- 360-degree swivel head
- High and low lumen output levels
- Up to 7 hours of runtime
- IP54 rated electronic enclosure
- Battery level indicator
- Lithium-ion battery charges via mini DC
- 5000K color temperature



LED HEAD LAMP

HL1030SW 300 LUMEN HEAD LIGHT

- 2 selectable beam angles
 - Flood: 300 30 lumen output
 - Spot: 120 lumens
- Up to 30 hours of runtime
- Smooth dimming feature by holding down the power button
- IP20 rated
- Includes (3) AAA Alkaline batteries
- Drop tested to 1 meter



