



Southwire™

RATCHETING LED WORK LIGHTS

1500 LUMEN RATCHETING LED WORK LIGHT

- Multi-Position Ratcheting Floor Stand
- 360 Degree Rotating Head
- On/Off Switch
- 18/3 SJTW Cord
- 5000K Color Temperature
- 1500 Lumens

3000 LUMEN RATCHETING LED WORK LIGHT

- Multi-Position Ratcheting Floor Stand
- 360 Degree Rotating Head
- On/Off Switch
- 18/3 SJTW Cord
- 5000K Color Temperature
- 3000 Lumens

5000 LUMEN RATCHETING LED WORK LIGHT

- Multi-Position Ratcheting Floor Stand
- 360 Degree Rotating Head
- On/Off Switch
- 18/3 SJTW Cord
- 5000K Color Temperature
- 5000 Lumens

10000 LUMEN RATCHETING LED WORK LIGHT

- Multi-Position Ratcheting Floor Stand
- 360 Degree Rotating Head
- On/Off Switch
- 18/3 SJTW Cord
- 5000K Color Temperature
- 10000 Lumens



MODEL #	UPC	DESCRIPTION	HEIGHT	WIDTH	LENGTH	WEIGHT
CSW1X1	032886747168	1500 Lumen Ratcheting LED Work Light	26"	7"	24.5"	2.7 lbs.
CSW3X1	032886747175	3000 Lumen Ratcheting LED Work Light	26"	7"	24.5"	2.7 lbs.
CSW5X1	032886747182	5000 Lumen Ratcheting LED Work Light	28"	8"	26.5"	3.7 lbs.
CSW10X1	032886747199	10000 Lumen Ratcheting LED Work Light	31.5"	9"	31.5"	4.7 lbs.

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2020 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.