



Southwire[®]
 WE DELIVER POWER... RESPONSIBLY*

PRODUCT DATA SHEET

Controlled Document – Engineering Drive

1530 Shields Drive
 Waukegan, IL 60085
 Toll-Free (800) 323-9355
 Fax: (847) 689-1192

PART NUMBER: 988299-xx-08

DESCRIPTION: RG-59/U COAXIAL CABLE WITH 95% COPPER BRAID

RATING: Mil-DTL-17

Construction Parameters:

		<u>Wall (in)*</u>	<u>OD (in)*</u>
Conductors:	23 AWG Solid Copper Covered Steel		0.0226
Dielectric:	Polyethylene color natural	0.062	0.146
Shielding:	95% Solid Bare Copper Braid		0.174
Jacket:	Type II Non Contaminating PVC	0.034	0.242

Electrical Properties:

	<u>VALUE*</u>
Impedance (ohms):	75
Capacitance (pF/ft):	22.0
Velocity of Propagation (%):	66
Attenuation** (db/100 ft):	
50 MHz	1.9
100 MHz	2.7
200 MHz	4.1
400 MHz	8.0
1000 MHz	13.0

Miscellaneous Information:

Jacket Color: Black
 Jacket Print (White): COLEMAN CABLE 988299 M17/29-RG059 MIL-DTL-17 OXDS2
 Ink Jet Print (Blue): XXXXXX (Date Code)
 "Coleman Cable LLC, is a wholly owned subsidiary of Southwire Company LLC"
 MIL-DTL-17: M17/29C-RG059
 Approx. Weight (lb/1000 ft): 35

This product complies with European Directive 2011/65/EU (RoHS-2)

On special orders the customer will accept all factory lengths and ± 10% of total order requested.

The information presented here is, to the best of our knowledge, true and accurate. However, since conditions of use are beyond our control, all recommendations or suggestions are presented without guarantee or responsibility on our part. We reserve the right to review and modify all constructions to conform with the latest Regulatory requirement. We disclaim all liability in connection with the use of information contained herein or otherwise. This specification is propriety intellectual property of SOUTHWIRE. Any information contained herein shall not be disclosed to any party without written consent of SOUTHWIRE.

Issued: 9/16/13

* = Nominal value
 By: RBC