



Southwire™

SIMPush™ EMT CONDUIT BODIES

LB TYPE - ALUMINUM

FEATURES

- No tool installation
- Reusable, test to 100 removal cycles
- Replaces traditional set screw and compression fittings
- Maintains grounding path

APPLICATIONS

- Allows access for inspection, pulling and maintenance

STANDARD MATERIAL

- Copper free aluminum

CERTIFICATIONS

- cULus Listed



E-LB-050

| STOCK # | MODEL # | SIZE | QUANTITY PER BAG | OVERALL PRODUCT DIMENSIONS | | | ASSOCIATED REMOVAL TOOL MODEL # | REMOVAL TOOL INCLUDED |
|----------------------------------|-----------|--------|------------------|----------------------------|--------|--------|---------------------------------|-----------------------|
| | | | | HEIGHT | WEIGHT | LENGTH | | |
| RETAIL POLY-BAG PACKAGING | | | | | | | | |
| 65074001 | E-LB-050 | 1/2" | 1 | 4.67" | 2.521" | 1.31" | E-RT-1P | --- |
| 65074101 | E-LB-075 | 3/4" | 1 | 5.505" | 2.855" | 1.53" | E-RT-1P | --- |
| 65074201 | E-LB-100 | 1" | 1 | 6.216" | 3.151" | 1.74" | E-RT-2P | --- |
| STOCK # | MODEL # | SIZE | QUANTITY PER BOX | HEIGHT | WEIGHT | LENGTH | ASSOCIATED REMOVAL TOOL MODEL # | REMOVAL TOOL INCLUDED |
| CONTRACTOR PACK | | | | | | | | |
| 65074002 | E-LB-050W | 1/2" | 8 | 4.67" | 2.521" | 1.31" | E-RT-1P | --- |
| 65074102 | E-LB-075W | 3/4" | 6 | 5.505" | 2.855" | 1.53" | E-RT-1P | --- |
| 65074202 | E-LB-100W | 1" | 4 | 6.216" | 3.151" | 1.74" | E-RT-2P | --- |
| 65074302 | E-LB-125W | 1-1/4" | 3 | 8.064" | 4.212" | 2.49" | E-RT-2P | --- |
| 65074402 | E-LB-150W | 1-1/2" | 3 | 8.335" | 4.633" | 2.49" | E-RT-3P | --- |
| 65074502 | E-LB-200W | 2" | 1 | 10.756" | 5.478" | 3.10" | E-RT-3P | --- |

Rev. 0, 03/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.