



HANG-A-LIGHT®

The next generation of temporary overhead lighting from Southwire is here with new integrated LED products. These new Southwire Hang-A-Light® models are ready to be hung right out of the box, with no assembly required. Once installed, they will distribute either 13,000 or 19,500 lumens around your jobsite, giving you the light you need to get the job done safely and efficiently. The Extended Whip LED lanterns provide you with the convenience of 35ft and 45ft of power cords, along with a 1 foot cord & receptacle outlet to daisychain multiple units.



INPUT: 16/3 CORD WITH 5-15 PLUG

OUTPUT: 1FT 16/3 CORD WITH DAISYCHAIN RECEPTACLE

STAINLESS STEEL CAGE

INTEGRATED HOOK WITH HANDLE FOR CEILING MOUNT

NO ASSEMBLY REQUIRED

5000K CCT / 80 CRI



MODEL #	UPC#	DESCRIPTION	VOLTS	WATTS	DIAMETER	HEIGHT	WEIGHT
T60100	032886792472	13,000 Lumen LED Overhead 10ft Cord	120/277	100	6.5"	11.4"	6.5 lbs
T60100W35	032886730771	13,000 Lumen LED Overhead 35ft Cord	120/277	100	6.5"	11.4"	7.6 lbs
T60150	032886792489	19,500 Lumen LED Overhead 10ft Cord	120/277	150	6.5"	12.7"	7.75 lbs
T60150W45	032886730788	19,500 Lumen LED Overhead 45ft Cord	120/277	150	6.5"	12.7"	8.9 lbs

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRETOOLS.COM

©2019 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.