



# Southwire™

## BX, FLEX CONNECTORS

### STRAIGHT - SQUEEZE TYPE - ZINC DIE CAST

#### FEATURES

- Squeeze type straight
- Available with insulated throat

#### APPLICATION

- Indoor use only
- In a dry location, use to connect flexible metallic conduit and steel AC cable to a steel outlet box, load center or other metal enclosure
- The 3/8" can also be used with steel and aluminum MC cable
- 3/8" size fits 1/2" knockout
- Suitable for: 3/8" steel flexible conduit, #14/2 metal conduit and #4–2 wire steel armored cable, 3/4" steel flexible metal conduit and #6–3 wire steel armored cable, 1" steel and reduced wall steel flexible metal conduit and #2–2 wire steel armored cable and 1-1/4"– 4" steel flexible metal conduit

#### STANDARD MATERIAL

- Zinc die cast


#### CERTIFICATIONS

- UL Standard: UL 514B
- Fed. Spec: W-F-406E, W-F-406D
- NEMA: FB 1-2014



150

PART #	CONDUIT SIZE	INNER QTY.	MASTER QTY.	WEIGHT/CASE (LBS.)	A	B (MIN. – MAX.)	C	SCREWS
150	3/8" 1/2" KO	50	500	35	1"	.58" – .61"	.37"	1
151TZ	1/2"	25	250	25	1.47"	.74" – .95"	.40"	1
152	3/4"	25	250	32	1.58"	.88" – 1.11"	.40"	1
153	1"	10	100	20	1.75"	1.14" – 1.38"	.54"	1
154	1-1/4"	10	100	29	1.91"	1.42" – 1.65"	.64"	1
155	1-1/2"	5	50	20	2.09"	1.68" – 1.94"	.75"	1
156	2"	10	40	21	2.34"	2.08" – 2.56"	.74"	1
157	2-1/2"	---	10	9	2.81"	2.85" – 3.25"	.875"	2
158	3"	---	10	17	3.84"	3.33" – 3.63"	1.03"	2
159	3-1/2"	---	1	3	4.19"	3.75" – 4.10"	1.03"	2
160TZ	4"	---	1	3	4.56"	4.18" – 4.58"	1.03"	2



Rev. 0, 03/23

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.