



Southwire[®]

TCC9/TCC9D

CRIMPING PLIERS

These high leverage crimping pliers have two die positions that permit the tool to crimp insulated and non-insulated terminals and ferrules.



● **TAPERED NOSE**

For working in confined spaces

● **CRIMPS**

Insulated and non-insulated terminals and connectors

● **COMFORTABLE GRIPS**

Curved handle and ergonomic molded grip for comfortable use

● **HEAVY DUTY CUTTING**

Specially hardened wire cutter in nose

● **DIPPED GRIP**

Curved handle and ergonomic dipped grip for comfortable use



Southwire[™]

TOOLS & EQUIPMENT

[BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.]

1-855-SWTOOLS
(855-798-6657)



Southwiretools.com



Features & Benefits

- Curved handle and ergonomic molded or dipped grip for comfortable use
- 10-22 AWG solderless terminals and connectors
- Crimps insulated and non-insulated terminals and connectors
- Specially hardened wire cutter in nose
- Tapered nose for working in confined spaces

Specifications

MODEL #	STOCK #	DESCRIPTION	HEIGHT	WIDTH	DEPTH	WEIGHT	HANDLE FINISH	HANDLE COLOR	INSULATED AND NON-INSULATED CRIMPING CAPACITY
TCC9	589936	Terminal Crimper Cutter	9.5"	1.75"	0.75"	14 oz	Comfort Grip	Yellow/Blk	10-22 AWG Solid (Solderless)
TCC9D	582899	Terminal Crimper Cutter Dip Handle	9.5"	1.75"	0.75"	12 oz	Dipped Grip	Yellow	10-22 AWG Solid (Solderless)

