



Southwire™

4" ROUND SWIVEL FIXTURE HANGERS

20° MAX SWING FROM VERTICAL

FEATURES

- Keyhole slots allow for fast installation
- SC-5075HFR features hinged door design that allows the installer to mount the cover on box and hang fixtures in one easy step
- Wire termination can be completed with the door open reducing time and labor expenses

APPLICATIONS

- 4" round swivel fixture hangers are used to hang commercial or industrial lighting fixtures, security cameras, motion detectors, occupancy sensors and other electrical/electronic devices from overhead ceiling installations
- Perfect for commercial or industrial applications where the pipe stem or fixture might be subjected to motion or vibration

STANDARD MATERIAL

- Galvanized steel

CERTIFICATIONS

- UL, cULus Listed



SC-5075HFR



PART #	DESCRIPTION	FITS CONDUIT	MASTER QTY.
SC-5075HFR	HANDS-FREE WIRING OF FIXTURE	1/2" OR 3/4"	25
SC-50R	STANDARD TYPE	1/2" ONLY	25
SC-75R	STANDARD TYPE	3/4" ONLY	25
GSCR-5075	STANDARD TYPE WITH GROUND PIGTAIL	1/2" OR 3/4"	25
MFHR50-75	STANDARD TYPE	1/2" OR 3/4"	10
33R	STANDARD TYPE	1/2" OR 3/4"	25

Painted covers from UL Listed material

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



Southwire™

4" ROUND PAN BOX, FIXTURE RINGS

FIXTURE EARS 2-3/4" ON CENTER



SC-50R



SC-75R



GSCR-5075



33R

Rev. 1, 3/24

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.