

LED Decorative Candelabra Series

FLAME AND BLUNT TIP



Give Your Home a Cozy Look and Feel

Topaz LED Decorative candelabra lamps are the energy savings alternative to traditional lighting. Available in blunt or flame tip configurations and offered in aesthetically pleasing warm 2700K and 3000K color temperatures. Dimmable for complete ambiance control and additional energy and maintenance savings. A long lasting direct replacement for incandescent lamps in ceiling fans, wall sconces and chandeliers.

FEATURES

- Blunt tip and flame tip models available
- Filament style best replicates the aesthetic appeal of incandescent lamps
- Up to 90% energy savings over incandescent
- Long life - up to 10X longer than traditional incandescents
- RoHS compliant and mercury free

SUGGESTED APPLICATIONS

- Decorative lighting, wall sconces, chandeliers
- Residential, hospitality, commercial



LED Decorative Candelabra Series FLAME AND BLUNT TIP

GENERAL SPECIFICATIONS

Input Voltage: 120V
THD: <15%
Minimum CRI: 80
Ambient Operating Temperature: -4°F to 104°F



SPECIFICATIONS / ORDER INFO

Catalog Number	Order Code	UPC	Wattage	Base	CCT	Lumens	Functional Life (L70)	MOL	Equiv. Wattage	ENERGY STAR	PK-QTY
Clear											
LCTC/3/830/D	79981	751338097766	3W	E12	3000K	165	25,000	3.8"	25W	-	1/20/100
LETC/3/830/D	79989	751338097827	3W	E26	3000K	165	25,000	3.8"	25W	-	1/20/100
LCFC/5/830/D	78914	751338002197	4.7W	E12**	3000K	315	25,000	4.6"	40W	-	1/20/100
LCTC/5/830/D	79896	751338001800	4.7W	E12**	3000K	315	25,000	4.2"	40W	-	1/20/100
LCTC/7/827/D	79346	751338000971	6.5W	E12	2700K	500	25,000	4.5"	60W	-	1/20/100
LCTC/7/830/D	79348	751338000988	6.5W	E12	3000K	500	25,000	4.5"	60W	-	1/20/100
Frosted											
LCFF/5/830/F/D	70728	751338016675	4.5W	E12**	3000K	300	15,000	4.0"	40W	Y	1/12/48
LCTF/5/830/F/D	70729	751338016682	4.5W	E12**	3000K	300	15,000	3.9"	40W	Y	1/12/48

NOMENCLATURE

Example: LCTC/3/830/D
LCTC = LED Candelabra Torpedo E12 Base Clear / 3 = 3 Watt / 830 = 3000K / D = Dimmable

ENERGY SAVINGS

Catalog Number	LED Wattage	Incandescent Wattage Replacement	Watts Saved	Yearly Savings	5 Year Savings
Based on 8 hours/day and \$0.11/kWh					
LCTC/3/830/D	3W	25W	22W	\$7.07	\$35.33
LETC/3/830/D	3W	25W	22W	\$7.07	\$35.33
LCFF/5/830/F/D	4.5W	40W	35.5W	\$11.40	\$57.00
LCTF/5/830/F/D	4.5W	40W	35.5W	\$11.40	\$57.00
LCTC/5/830/D	4.7W	40W	35.3W	\$11.34	\$56.70
LCFC/5/830/D	4.7W	40W	35.3W	\$11.34	\$56.70
LCTC/7/827/D	6.5W	60W	53.5W	\$17.80	\$85.90
LCTC/7/830/D	6.5W	60W	53.5W	\$17.80	\$85.90

NOTES:

Not for Sale in California.

Dimming - This lamp is designed to be compatible with most leading edge or incandescent style rotary or slide type dimmers. (Dimming range 100% - 10%) Performance may vary depending on dimmer

** E26 Adapter included

This device is not intended for use with emergency exits.

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. Specifications subject to change without notice.

FIVE (5) YEAR LIMITED WARRANTY: TOPAZ LIGHTING CORP. warrants to the original purchaser that all TOPAZ LED lamps shall be free from defects of material and workmanship for a period of five (5) years from the date of purchase. Based on 12 hours of use per day. TOPAZ LIGHTING CORP. will, at its option, repair or replace without charge a defective LED lamp that has not been misused, carelessly handled or improperly installed. Repair or replacement, as stated above, shall constitute the purchaser's exclusive warranty, which does not extend to transportation, installation, labor or any other consequential charges. www.topaz-usa.com

Specifications subject to change without notice.

Rev. 1, 04/22