



Southwire™

TOP-FLEX 1 TUBING

NON-METALLIC - GRAY

FEATURES

- Resists corrosion, abrasion, oil, water, acid, metal shavings, and rough environments
- UL Type B flexible nonmetallic liquidtight conduit

APPLICATION

- Indoor or outdoor use
- Hazardous Locations - where necessary for flexible connections within hazardous locations per the following:
 - Class 1, Div. 2 - 2005 NEC 501.10(B)(2)
 - Class 2, Div. 1 - 2005 NEC 502.10(A)(2)
 - Class 2, Div. 2 - 2005 NEC 502.10(B)(2)
 - Class 3, Div. 1 - 2005 NEC 503.10(A)(2)
 - Class 3, Div. 2 - 2005 NEC 503.10(B)

STANDARD MATERIAL

- Integral Rigid and flexible PVC construction

CERTIFICATIONS

- cULus


HF112

UL TYPE B FLEXIBLE NONMETALLIC LIQUIDTIGHT CONDUIT

- 3/8" through 2" trade sizes
- Use with top-flex nylon connectors straight or right angle
- May also be used with Topaz Die Cast Connectors for liquidtight conduit
- Resists corrosion, abrasion, oil, water, acid, metal shavings, and rough environments
- Resists abuse, pull, and crushing
- Smoothinside for easier wire pulling, no hazardous sharp edges or burrs; will not damage conductors
- For direct burial/poured concrete
- Lightweight and lower installed cost
- Quick installation, cuts with utility knife or PVC cutter (CATALOG #VF28)
- Integral Rigid and flexible PVC construction
- Suitable for indoor/outdoor use:
 - HVAC equipment
 - machine tools
 - motors and controls
 - marine equipment
 - printing equipment
 - pumps refrigeration equipment
- UV rated
- 80° C

PART #	SIZE	INNER QTY.	MASTER QTY.	WEIGHT/ CASE (LBS.)	OUTSIDE DIAMETER		INSIDE DIAMETER		WALL THICKNESS
					MIN.	MAX.	MIN.	MAX.	
HF138	3/8"	---	100'	10	.69"	.71"	.484"	.504"	.21"
HF112	1/2"	---	100'	13	.82"	.84"	.622"	.642"	.21"
HF112R	1/2"	REEL	1000'	130	.82"	.84"	.622"	.642"	.21"
HF134	3/4"	---	100'	18	1.03"	1.05"	.82"	.84"	.21"
HF134R	3/4"	REEL	800'	144	1.03"	1.05"	.82"	.84"	.21"
HF11	1"	---	100'	25	1.29"	1.315"	1.041"	1.066"	.25"
HF11R	1"	REEL	500'	160	1.29"	1.315"	1.041"	1.066"	.25"
HF1114	1-1/4"	---	100'	33	1.63"	1.66"	1.38"	1.41"	.25"
HF1112	1-1/2"	---	50'	23	1.865"	1.90"	1.575"	1.60"	.30"
HF12	2"	---	50'	30	2.34"	2.375"	2.02"	2.045"	.33"

Rev. 0, 01/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

 ©2023 Southwire Company, LLC. All rights reserved.
 *Registered Trademark & ™Trademark of Southwire Company, LLC.