



Southwire™

SIMPush™ RIGID CONDUIT BODIES

LR TYPE - ALUMINUM

FEATURES

- Gasket NBR Nitrile
- No need to thread conduit
- Works with threaded or non-threaded RMC, IMC, GRC, ARC and rigid stainless steel
- Copper free aluminum, powder coat
- Reusable, tested for up to 100 removal cycles
- Watertight, concrete tight, direct burial rated

APPLICATIONS

- Allows access for inspection, pulling and maintenance

STANDARD MATERIAL

- Copper free aluminum

CERTIFICATIONS

- UL Listed, 514B, IP66, NEMA 4X



R-LR-050

STOCK #	MODEL #	SIZE	QUANTITY PER BAG	OVERALL PRODUCT DIMENSIONS			ASSOCIATED REMOVAL TOOL MODEL #	REMOVAL TOOL INCLUDED
				HEIGHT	WEIGHT	LENGTH		
RETAIL POLY-BAG PACKAGING								
65081501	R-LR-050	1/2"	1	5.34"	2.83"	1.40"	R-RT-1P	---
65081601	R-LR-075	3/4"	1	6.11"	3.09"	1.64"	R-RT-1P	---
STOCK #	MODEL #	SIZE	QUANTITY PER BOX	HEIGHT	WEIGHT	LENGTH	ASSOCIATED REMOVAL TOOL MODEL #	REMOVAL TOOL INCLUDED
CONTRACTOR PACK								
65081502	R-LR-050W	1/2"	4	5.34"	2.83"	1.40"	R-RT-1P	---
65081602	R-LR-075W	3/4"	4	6.11"	3.09"	1.64"	R-RT-1P	---
65081702	R-LR-100W	1"	4	6.99"	3.33"	1.90"	R-RT-2P	---
65081802	R-LR-125W	1-1/4"	3	9.02"	4.53"	2.85"	R-RT-2P	---
65081902	R-LR-150W	1-1/2"	3	9.05"	4.56"	2.85"	R-RT-3P	---

Rev. 0, 06/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.