



LED LINEAR WRAP UTILITY

SUGGESTED APPLICATIONS

- Commercial, residential
- Garages, workshops, basements, general task lighting
- Stairways and corridors
- Suitable for use in closets: Compliant with NFPA 70 NEC section 410.16 (A)(3) and 410.16 (C)(5)

FEATURES

- Efficient replacement for traditional fluorescent fixtures
- Side ½" knockouts allow easy access connection for wire and conduit
- Smooth 0-10V dimming, down to 10%
- Durable white steel housing with prismatic polycarbonate lens
- Surface mount hardware included
- Available in 2' and 4' length and 4000K and 5000K CCT



INPUT VOLTAGE: 120-277V

FREQUENCY: 50/60HZ

**POWER FACTOR, THD %:
>0.9;<20%**


**DIMMABLE: 0-10V,
DOWN TO 10%**

EFFICACY: 115 LPW

MINIMUM CRI: 80

BEAM ANGLE: 105°

**FUNCTIONAL LIFE (L70):
50,000 HOURS**



**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

800-666-2852 | TOPAZ-USA.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.



LED LINEAR WRAP UTILITY

ITEM SPECIFICATIONS | ORDER INFO

MODEL #	ORDER CODE	UPC	SIZE (TRADE)	LUMENS	WATTAGE	INPUT CURRENT @120V/277V	CCT	DLC ID
LWRAPU2-20-40K-D	74430	032886305375	2FT	2,300	20W	0.21/0.09A	4000K	S-0VVCE4
LWRAPU2-20-50K-D	74431	032886305382	2FT	2,300	20W	0.21/0.09A	5000K	S-PX10Q6
LWRAPU4-40-40K-D	74428	032886304781	4FT	4,600	40W	0.40/0.19A	4000K	S-0B1MAL
LWRAPU4-40-50K-D	74429	032886304798	4FT	4,600	40W	0.40/0.19A	5000K	S-5AQVIF

NOMENCLATURE

Example: LWRAPU4-40-40K-D

PRODUCT	SIZE	WATTAGE	CCT	OPTIONS
LWRAPU = LINEAR WRAP-UTILITY	2FT 4FT	20W 40W	4000K 5000K	D= DIMMABLE

ACCESSORIES (SOLD SEPARATELY)

MODEL #	ORDER CODE	UPC	DESCRIPTION
BEL4W-UNV	72764	---	LED Emergency Driver
WD-OS	72700	751338004931	Occupancy Sensor

ENERGY SAVINGS Based on 12 hours/day and \$0.11/kWh

MODEL #	LED WATTAGE	FLUORESCENT REPLACEMENT WATTAGE	WATTS SAVED	YEARLY SAVINGS	5 YEAR SAVINGS
LWRAPU2-40-xxK-D	20W	2x 17W T8	14W	\$7	\$34
LWRAPU4-40-xxK-D	40W	2x 32W T8	20W	\$10	\$48



Job Name/Title: _____

Model #: _____

Contractor: _____



LED LINEAR WRAP UTILITY

DIMENSIONS | WEIGHT

MODEL #	A (IN)	B (IN)	C (IN)	WEIGHT (LBS)
LWRAPU2-20-XXK-D	24.84	5.19	2.37	1.89
LWRAPU4-40-XXK-D	48.74	5.19	2.37	3.19



NOTES

DLC Primary Use - Direct Linear Ambient Luminaires
Dimming with standard 0-10V control system or wall dimmers. Dimming complies with IEC60929 Annex E. Fixture may not be compatible with all dimmers. Dimming performance may vary based on selected dimmer. Visit www.topaz-usa.com/led-dimmer-compatibility for up-to-date dimmer compatibility information.

FIVE (5) YEAR LIMITED WARRANTY: SOUTHWIRE COMPANY, LLC. For details visit: <https://southwire.com/resources/warranties>

This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation.

Specifications are subject to change without prior notice. Replacement wattage shown depends on application and fixture.



800-666-2852 | TOPAZ-USA.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.