



Southwire™

SIMPush™ NON-METALLIC LIQUIDTIGHT 90° CONNECTOR

PVC

FEATURES

- Simple fast push on installation
- Works with Type B nonmetallic flexible liquidtight conduit
- UV resistant PVC
- Reusable, tested for up to 100 removal cycles
- Watertight, concrete tight, direct burial rated

APPLICATIONS

- Quickly connects nonmetallic liquidtight to box or enclosure at 90° angle

STANDARD MATERIAL

- PVC

CERTIFICATIONS

- cULus Listed, IP66, NEMA 4X



LTNM-90-050



STOCK #	MODEL #	SIZE	QUANTITY PER BAG	OVERALL PRODUCT DIMENSIONS			ASSOCIATED REMOVAL TOOL MODEL #	REMOVAL TOOL INCLUDED
				HEIGHT	WEIGHT	LENGTH		
RETAIL POLY-BAG PACKAGING								
67600201	LTNM-90-050	1/2"	1	2.735"	1.419"	2.735"	PLT-RT-1P	---
67600203	LTNM-90-050-Q5	1/2"	5	2.735"	1.419"	2.735"	PLT-RT-1P	---
67600301	LTNM-90-075	3/4"	1	2.985"	1.653"	2.985"	PLT-RT-1P	---
67600401	LTNM-90-100	1"	1	3.254"	1.929"	3.254"	PLT-RT-100	---
STOCK #	MODEL #	SIZE	QUANTITY PER BOX	HEIGHT	WEIGHT	LENGTH	ASSOCIATED REMOVAL TOOL MODEL #	REMOVAL TOOL INCLUDED
CONTRACTOR PACK								
67600202	LTNM-90-050WT	1/2"	24	2.735"	1.419"	2.735"	PLT-RT-1P	YES
67600302	LTNM-90-075WT	3/4"	15	2.985"	1.653"	2.985"	PLT-RT-1P	YES
67600402	LTNM-90-100WT	1"	9	3.254"	1.929"	3.254"	PLT-RT-100	YES

Rev. 0, 06/23

**BUILT FOR DURABILITY.
BUILT FOR RELIABILITY.
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2023 Southwire Company, LLC. All rights reserved.
*Registered Trademark & ™Trademark of Southwire Company, LLC.