



# Southwire™

## REEL MAC THE REEL JACK™ REEL STANDS

Southwire™ brings you the best built, best value reel jack you can buy. Reel Mac The Reel Jack™ jack stands are available in three styles. Style numbers 60 and 70 feature screw-type adjustment with large 1-1/2" screws and large, easy to use handles. Style number 80 features a heavy duty ratchet handle.

### FEATURES

- All steel construction
- Powder coat finish for superior durability and corrosion resistance
- Dependable Southwire™ quality
- Extra strength double locking pin for quick set up

#### NO. 60 (#780941)

Screw-type telescoping reel jack for 26" to 56" diameter reels

#### NO. 70 (#780942)

Screw-type telescoping reel jack for 46" to 96" diameter reels

#### NO. 80 (#780943)

Heavy duty ratchet drive reel jack for reels up to 90" in diameter. Convenient, detachable ratchet handle stores in base when not in use



### ACCESSORIES

Southwire Reel Mac™ Spindles are designed to be used with Southwire Reel Mac™ Jack Stands.

MODEL #	STOCK #	DESCRIPTION	HEIGHT RANGE	LOAD CAPACITY	USE WITH SPINDLE	WEIGHT
RM60	780941	Reel Mac™ No. 60	13" - 27" (33 - 68 cm)	2,500 lbs (1,135 kg)	61	30 lbs (13.6 kg)
RM70	780942	Reel Mac™ No. 70	21" - 54" (53 - 137 cm)	2,500 lbs (1,135 kg)	71	51 lbs (23.1 kg)
RM80	780943	Reel Mac™ No. 80	28" - 45" (71 - 114 cm)	3,700 lbs (1,700 kg)	81	105 lbs (47.6 kg)
MODEL #	STOCK #	SPINDLE #	LENGTH	LOAD CAPACITY	DIAMETER	WEIGHT
SA61	780229	61	62.0" (157.5 cm)	5,000 lbs (2,270 kg)	2.375" (6.0 cm)	37 lbs (16.8 kg)
SA71	780230	71	76.0" (193.0 cm)	5,000 lbs (2,270 kg)	2.375" (6.0 cm)	47 lbs (21.3 kg)
SA81	780231	81	100.0" (254.0 cm)	7,500 lbs (3,400 kg)	3.5" (8.9 cm)	118 lbs (53.5 kg)

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

**1-855-798-6657 | SOUTHWIRE.COM**

©2025 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.