



# Southwire™

## 4" X 2" HANDY/UTILITY BOX

### 2-1/8" DEEP - DRAWN WITH CONDUIT KNOCKOUTS

#### FEATURES

- Raised ground provision ensures ground screw will not interfere with wall surface (reference table)

#### APPLICATIONS

- Handy utility boxes are used for convenience outlets, switches and small junction boxes in exposed work applications

#### STANDARD MATERIAL

- Galvanized steel or 316 stainless steel

#### CERTIFICATIONS

- UL Listed



G19282



G19282NGH



G19282-3/4



G19282-BLNK



G19282-BLNKSS



G19282-SS

PART #	DESCRIPTION	KNOCKOUTS		CUBIC INCHES (CM <sup>3</sup> )	MASTER QTY.
		SIDE CONDUIT	BOTTOM CONDUIT		
G19282	RAISED GROUND	(8) 1/2"	(2) 1/2"	13.5 (221.2)	50
G19282NGH	FLAT BOTTOM	(8) 1/2"	(3) 1/2"	13.5 (221.2)	50
G19282-3/4	RAISED GROUND	(6) 3/4"	(2) 1/2"	13.5 (221.2)	50
G19282-BLNK	BLANK, NO KO'S	---	---	13.5 (221.2)	50
G19282-BLNKSS	BLANK, 316 STAINLESS STEEL	---	---	13.5 (221.2)	50
G19282-SS	RAISED GROUND, 316 STAINLESS STEEL	(8) 1/2"	(2) 1/2"	13.5 (221.2)	50
G19282-1/2-3/4	FLAT BOTTOM	(6) 1/2" AND (2) 3/4"	(2) 1/2"	13.5 (221.2)	50

Rev. 1, 3/24

**BUILT FOR DURABILITY.  
BUILT FOR RELIABILITY.  
BUILT FOR WORK.™**

1-855-798-6657 | SOUTHWIRE.COM

©2024 Southwire Company, LLC. All rights reserved.  
\*Registered Trademark & ™Trademark of Southwire Company, LLC.