

SERIES 2615 THE BIG LIFT

APPLICATIONS

- 15' (3-4.6 m)
- 1,100 lbs (500 kg) capacity
- 2 speed winch
- Travels through doorways
- Legs fold for compact storage
- Rolls into vehicles
- Adjustable steering level handle
- Legs unlock with plunger pin and fold up for storage. Roller wheels under each leg for ease of moving lift in stored position
- Aluminum pulleys enclosed to prevent cable from coming off
- Mast hold bar for horizontal transportation. Hold down bar can be reshaped if bent.
- Rugged two speed winch makes lifting heavy loads a snap
- Mast roller wheels help to roll lift into vehicles
- Nifty lifting hook for crane use
- Available in yellow powdercoat, or galvanized for improved oxidation resistance

ACCESSORIES

ADJUSTABLE STEERING HANDLE

Adjustable steering handle that pops out of way with push button.

OUTRIGGER LOCKING MECHANISM

Locks legs both in stored or operating position.

REVERSED FORK

Forks can easily be reversed to achieve greater height using plunger pins

FORK EXTENSIONS

With push of a button, optional fork extensions extend forks extra 8" (20 cm). Extensions store in forks. Extension capacity 450 lbs (205 kg).



PART #	DESCRIPTION	LOAD CAPACITY	LIFTING HEIGHT, FORKS DOWN	LIFTING HEIGHT, FORKS REVERSED	EQUIPMENT WEIGHT	MIN LOAD HEIGHT	GROUND CLEARANCE
783067	2615 LIFT, POWDERCOAT YELLOW	1100 lbs (500 kg)	14' 5" (4.4 m)	16' 5" (5 m)	346 lbs (157 kg)	4" (10 cm)	2.5" (6.4 cm)
783068	2615 LIFT, GALVANIZED COATING	1100 lbs (500 kg)	14' 5" (4.4 m)	16' 5" (5 m)	461 lbs (209 kg)	4" (10 cm)	2.5" (6.4 cm)
784569	PIPE CRADLE ASSEMBLY, 2600 LIFT (1 PAIR)	1100 lbs (500 kg)	---	---	---	---	---
783163	FORK EXTENSION KIT, 2600 SERIES LIFTS	450 lbs (204 kg)	---	---	---	---	---